


64-channel (± 100 V / -200 to 0 V / 0 to 200 V), low harmonic distortion, high voltage analog independent switches



Features

- 200 V peak-to-peak input and output signal
- Three different operating ranges:
 - From -100 V to +100 V
 - From 0 V to 200 V
 - From -200 V to 0 V
- Very fast input slew rate (40 V/ns without load)
- Only +3.3 V low voltage supply
- Rail-to-rail input signal
- Low on-resistance
- Very low cross-talk between channels
- Low parasitic capacitance
- 42 k Ω bleed resistor on the outputs
- Thermal and undervoltage protection
- Latch-up free
- Control through serial interface
- 20 MHz data shift clock frequency
- Cascadable serial register with latches

Applications

- Medical ultrasound imaging
- NDT ultrasound transmission
- Piezoelectric transducer drivers
- Industrial

Description

The STHV64SW is an integrated circuit which features 64 independent switches. It is designed for medical ultrasound applications, but can also be used for driving piezoelectric, capacitive or MEMS transducers, and in industrial application such as generic high voltage switches.

The STHV64SW comprises a shift register for serial communication, self-biased high voltage MOSFET gate drivers, high power N-channel MOSFETs, bleed resistance for each switch, thermal sensor and undervoltage lockout. Moreover, the STHV64SW includes self-biasing and thermal shutdown blocks. The switches are capable of providing up to ± 3 A peak output current.

Product status link	
STHV64SW	
Product summary	
Order code	STHV64SW
Package	BGA-196
Packing	Tray

Table 1. Document revision history

Date	Version	Changes
01-Mar-2019	1	Initial version

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2019 STMicroelectronics – All rights reserved