




Connectors > Contacts > Connector Contacts > D-Sub Connector Contacts: Pin, Brass, Signal, Size 20



Contact Type: **Pin**

Contact Mating Area Plating Material: **Gold Flash**

Contact Retention Type Within Housing: **Snap-In**

Contact Size: **Size 20**

Wire Size: **28 – 24 AWG**

[All D-Sub Connector Contacts: Pin, Brass, Signal, Size 20 \(45\)](#)

Features

Contact Features

Contact Underplating Material	Nickel
Mating Pin Diameter	1.02 mm[.04 in]
PCB Contact Termination Area Plating Material	Tin
	100 µin
Contact Type	Pin
Contact Mating Area Plating Material	Gold Flash
Contact Size	Size 20
Contact Base Material	Brass
Contact Current Rating (Max)	1.2 A

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable



Mechanical Attachment

Wire Insulation Support	With
Contact Retention Type Within Housing	Snap-In

Dimensions

Compatible Insulation Diameter Range	1.27 – 1.52 mm[.05 – .06 in]
Wire Size	.08 – .2 mm ²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Identification Marking

Contact Color Code	Black
--------------------	-------

Packaging Features

Packaging Method	Reel
Packaging Quantity	10000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 206226-1 CPC PLUG ASSEMBLY SIZE 23-7	 TE Part # 206136-1 CPC PLUG ASSEMBLY SIZE 23-7	 TE Part # 206126-1 CPC PLUG ASSEMBLY SIZE 17-28	 TE Part # 7-2837445-7 OCEAN_2.0_SPARE_PART_KIT-042F062O
 TE Part # 2837445-2 OCEAN_2.0_Applicator-S-042F062OA-RSA	 TE Part # 205838-1 CPC PLUG ASSEMBLY SIZE 11-8	 TE Part # 206039-1 CPC PLUG ASSEMBLY SIZE 17-28	 TE Part # 206434-1 CPC PLUG ASSEMBLY SIZE 11-8
 TE Part # 206485-1 CPC PLUG ASSEMBLY SIZE 11-9	 TE Part # 206437-1 CPC PLUG ASSEMBLY SIZE 23-57	 TE Part # 206426-1 CPC PLUG ASSEMBLY SIZE 17-3	

Also in the Series | Circular Plastic Connectors Series 2

 Circular Power Connectors(36)	 Connector Contacts(52)
--	--

Customers Also Bought



TE Part #640392-1
.062 COMM P&S SOK 24-30 PTPBR

TE Part #770361-1
06P .093 COMM P&S PLUG .250CL

TE Part #CAT-035-DCCPB20
D-Sub Connector Contacts: Pin, Brass, Signal, Size 20

TE Part #87499-8
04 MODIV HSG COMP SR .100CL

TE Part #NB09012001
ATUM-12/3-0-STK

TE Part #1734205-1
MINI USB, TYPE B, PLUG. CABLE-KIT

TE Part #321021
PIDG RING (26-22)

TE Part #3-350819-2
ULTRA-FAST 250 ASY REC 16-14 AWG TPBR

Documents

Product Drawings

CONT,PIN,PLATED,20DF,STRIP,#24-28

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5066682-6_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5066682-6_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5066682-6_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications

English

Signal Contacts

English

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English



Product Specifications

Application Specification

English

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English