



**FAG****6311-C-C4**

Deep groove ball bearing

Deep groove ball bearing 63...-C, single row,
Generation C, steel sheet metal cage

Technical information



Your current product variant

Changed internal design	C	GenerationC
Sealing	Without	Not sealed
Cage	JN	Steel sheet metal
Tolerance class	P6	Class6 (P6), better than PN
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	Without	Bearing not greased
Radial internal clearance	C4 (Group 4)	Internal clearance larger than C3
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	55 mm	Bore diameter
D	120 mm	Outside diameter
B	29 mm	Width
C _r	83,000 N	Basic dynamic load rating, radial
C _{0r}	47,500 N	Basic static load rating, radial
C _{ur}	3,300 N	Fatigue load limit, radial
n _G	8,500 1/min	Limiting speed
n _{gr}	7,800 1/min	Reference speed
≈m	1.297 kg	Weight



Mounting dimensions

$d_{a\ min}$	66 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	109 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	2 mm	Maximum fillet radius

Dimensions

$r_{\ min}$	2 mm	Minimum chamfer dimension
D_1	102.15 mm	Shoulder diameter outer ring
D_2	105.3 mm	Caliber diameter outer ring
d_1	74.7 mm	Shoulder diameter inner ring
d_2	72.54 mm	Caliber diameter inner ring

Temperature range

$T_{\ min}$	-30 °C	Operating temperature min.
$T_{\ max}$	150 °C	Operating temperature max.

Calculation factors

f_0	12.9	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed