

TST11DGRA1D04

x OBSOLETE

Alcoswitch

TE Internal #: 1825455-3

TE Internal Description: TST11DGRA1D04

[View on TE.com >](#)



Switches > Toggle Switches



Contact Current Rating: **.4 A**

Configuration (Pole-Throw): **Single Pole - Double Throw**

Operating Function: **On None On**

Operating Voltage: **20 VDC**

Product Orientation: **Right Angle**

Features

Product Type Features

Sealed Device	Yes
Toggle Style	Baton Short
Switch Type	Toggle Switch

Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On None On

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	1000 VAC
Insulation Resistance	1000 MΩ
Contact Current Rating	.4 A
Operating Voltage	20 VDC

Body Features

Product Orientation	Right Angle
Bushing Style	Unthreaded

Contact Features

Contact Base Material	Brass
Switch Contact Plating Material	Gold over Nickel

Housing Features

Process Sealed	Yes
----------------	-----



Dimensions

Toggle Length	5.23 mm[.206 in]
---------------	------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought


TE Part #2-1586042-2
22P VAL-U-LOK R/A HDR V0

TE Part #2344655-5
PCB ANT, MHF 4, 50mm, Wi-Fi TRIPLE BAND

TE Part #5747813-4
15 MSFL RCPT RA 590L(IN,FM,BL)

TE Part #5102162-8
A/L UNIV HDR 34P RA





TE Part #796645-4
4POS 5.0MM CE R/A HDR,TRM BLK



TE Part #1735481-4
0.8FH,R17H.5,100,08/Sn,TU,SC



TE Part #5745351-2
09 PLUG RA/MS STD



TE Part #1-644487-2
12P MTA100 SHRD HDR ASSY 30AU



TE Part #1-640454-9
19P MTA100 HDR ASSY SQ STR POL

Documents

Product Drawings

TST11DGRA1D04

English

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English