



WRECKER 230mm x 7/11 Tpi - 5 pc

MULTI MATERIAL: HEAVY DUTY WRECKER™ BLADES

- Strong and precise: Thick 1.27 mm blade body.
- Bi-Metal construction: Excellent blade life and performance.
- Tooth geometry: Aggressive strengthened tooth tip design and uniform gullet depth allows for more material to be removed per stroke for faster cutting.
- Blade shape: Sloped - The sloped shape makes this blade ideal for plunge cutting. Most suited for cutting metal and for demolition applications (wood with nails).



Article Number	48475706
Blade length (mm)	230
Materials suited for	Thick metal > 4 mm Medium metal 1.5 - 4 mm Non ferrous metal (Cu/Al) Wood with nails & screws
Max. cutting capacity cast iron pipes [mm]	ø 10 - 175
Max. cutting capacity metal pipe	ø 10 - 175
Max. cutting capacity non ferrous metals [mm]	4 - 10
Max. cutting capacity steel (mm)	4 - 10