



Geberit Mapress Carbon Steel flange PN 6, with pressing socket



Example image



APPLICATION PURPOSES

- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water $\leq 120^\circ\text{C}$
- For extinguishing water (wet)
- For sprinklers (wet)
- For compressed air (oil purity class 3)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Outside zinc-plated
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug
- Design B1 (raised sealing strip with standard sealing strip), EN 1092-1

TECHNICAL DATA

Product material Non-alloy steel 1.0034 E195 (EN 10305)

ACCESSORIES

- Geberit bolt set for flange connection, made of zinc-plated steel
- Geberit flange gasket, fibre composite material PN 6

Art. no.	DN	d, ø mm	di, ø mm	D cm	k mm	m mm	L cm	l cm	Z cm	n pc.	PN bar
23744	20	22	19	9	65	11	6.1	1.4	4	4	6
23745	25	28	25	10	75	11	6.5	1.4	4.2	4	6
23746	32	35	32	12	90	14	6.8	1.4	4.2	4	6
23747	40	42	39	13	100	14	7.5	1.4	4.5	4	6

<i>Art. no.</i>	<i>DN</i>	<i>d, ø mm</i>	<i>di, ø mm</i>	<i>D cm</i>	<i>k mm</i>	<i>m mm</i>	<i>L cm</i>	<i>l cm</i>	<i>z cm</i>	<i>n pc.</i>	<i>PN bar</i>
23748	50	54	51	14	110	14	8.3	1.4	4.8	4	6
23749	65	76.1	72	16	130	14	11.4	1.4	6.1	4	6
23750	80	88.9	84.8	19	150	18	12.1	1.6	6.1	4	6
23751	100	108	103.9	21	170	18	12.6	1.6	5.1	4	6