

# Eaton 262549

Catalog Number: 262549

Eaton XIOC Analog input card for XC100/200, 24 V DC, 8AI (4-20mA)



### General specifications

#### Product Name

Eaton XIOC Accessory Input card

#### Catalog Number

262549

#### EAN

4015082625498

#### Product Length/Depth

100 mm

#### Product Height

95 mm

#### Product Width

30 mm

#### Product Weight

0.135 kg

#### Certifications

CSA-C22.2 No. 142-M

CSA File No.: 012528

CSA

CSA Class No.: 2252-01

UL File No.: E135462

CSA-C22.2 No. 0-M

UL508

IEC/EN 61131-2

UL

CE

EN 50178

UL Category Control No.: NRAQ

## Features & Functions

### Electric connection type

Screw-/spring clamp connection

### Features

Analog outputs configurable

Analog inputs configurable

Input, current

## General

### Admissible range

20.4 – 28.8 V (11.8 – 14.4 V), Power supply

### Current consumption

100 mA (typ.), internal (5 V DC), Inputs

### Degree of protection

IP20

### Number of channels

8, Input

### Overvoltage category

II

### Pollution degree

2

### Protection class

1

### Repetition rate

1 s

### Residual ripple

≤ 5 %

### Resolution

12 Bit (digital)

### Type

Analog module

### Used with

XC100/200 (expandable with up to 15 XI/OC modules)

## Ambient conditions, mechanical

### Impact resistance

500 g/ 50 mm ±25 g

### Shock resistance

15 g, Mechanical, Shock duration 11 ms

### Vibration resistance

10 - 57 Hz, ± 0.075 mm

57 - 150 Hz ± 1.0 mm

## Climatic environmental conditions

### Ambient operating temperature - min

0 °C

### Ambient operating temperature - max

55 °C

### Ambient storage temperature - min

-25 °C

### Ambient storage temperature - max

70 °C

## Electro magnetic compatibility

### Emitted interference

Class A (according to DIN/EN 55011/22)

### Voltage dips

10 ms

## Electrical rating

### Power loss

Max. 0.5 W

### Power supply

24 V DC (-15/+20 %), approx. 150 mA

### Rated operational voltage

24 (12) V DC

## Terminal capacities

### Terminals

Optionally, screw terminals  
or spring-loaded terminals  
for digital/analog modules  
Plug-in terminal block

## Communication

### Connection type

2-core screened cable ( $\leq 20$  m)

## Input/Output

### Conversions

$\leq 5$  ms

### Input

8 Inputs (4 - 20 mA)

### Input current

4 - 20 mA

### Number of inputs (analog)

8

### Number of outputs (analog)

0

### Total error

$\leq \pm 1$  % (of the full-scale value), Inputs

## Safety

### Explosion safety category for dust

None

### Explosion safety category for gas

None

### Potential isolation

Analog inputs: Opto-isolated

Analog outputs: no

## Design verification

### Equipment heat dissipation, current-dependent P<sub>vid</sub>

0 W

### Heat dissipation capacity P<sub>diss</sub>

0 W

### Heat dissipation per pole, current-dependent P<sub>vid</sub>

0 W

### Rated operational current for specified heat dissipation (I<sub>n</sub>)

0 A

Static heat dissipation, non-current-dependent Pvs

0.5 W

#### 10.2.2 Corrosion resistance

Meets the product standard's requirements.

#### 10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

#### 10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

#### 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

#### 10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

#### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.7 Inscriptions

Meets the product standard's requirements.

#### 10.3 Degree of protection of assemblies

Meets the product standard's requirements.

#### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

#### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

## Resources

### Brochures

[eaton-xc300-modular-plc-brochure-br050008en-en-us.pdf](#)

[Slice card modular I/O system for the machine building industry XN300 - brochure](#)

### Declarations of conformity

[DA-DC-00003821.pdf](#)

[DA-DC-00003397.pdf](#)

### Drawings

[eaton-electronic-devices-dimensions-xioc-output-module-dimensions.eps](#)

[eaton-electronic-devices-local-inputoutput-xioc-output-module-3d-drawing.eps](#)

[eaton-electronic-devices-in-out-module-xioc-output-module-dimensions.eps](#)

### eCAD model

[DA-CE-ETN.XIOC-8AI-I2](#)

### Manuals and user guides

[MN05002002Z\\_EN](#)

### mCAD model

[DA-CS-xioc](#)

[DA-CD-xioc](#)

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### 10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

#### 10.11 Short-circuit rating

Is the panel builder's responsibility.

#### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility.

#### 10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)