




Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3.5% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # CAT-ET36-M3113
12p man POE switch 1Gb



TE Part # CAT-ET36-M3113A
12p man POE switch rack



TE Part # CAT-ET36-M3113B
20p man POE switch 1Gb

Customers Also Bought



TE Part #1-2267795-6
CA, MTE FOW-FOW, 8POS, 300mm
15Au, 24AWG




TE Part #CONBNC004
BNC Jack 50 Ohm Panel Mount




TE Part #740072-000
SO63-3-01




TE Part #1-104482-8
40 SHORT PT RCPT HSG DR .100CL



TE Part #6-2176452-7
CPF 0201 2K61 0.1% 25ppm 1K RL



TE Part #629267-000
TXR40AB00-1608AI



TE Part #8-2176397-8
3502 4K3 1%



TE Part #5660014001
SFR-1/4-0-SP



TE Part #6-146256-2
24 MODII HDR DRST B/A .100CL LF



TE Part #972203-000
S03-02-R-100

Documents

- Product Drawings
- M12 A-M-8 CAB ASS. (PLG-PLG) 1.0M CAT 7
- English
- CAD Files
- 3D PDF
- 3D



Customer View Model

[ENG_CVM_CVM_2322423-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2322423-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2322423-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M12 CABLE ASSEMBLIES](#)

English