

FEATURES

- **LED Bulb Type:** Offers energy efficiency and long lifespan, reducing maintenance costs.
- **AC Current Type:** Compatible with standard AC power supplies, ensuring easy integration.
- **Grey ABS Housing:** Provides durability and resistance to impact, suitable for industrial use.
- **IP43 Rating:** Protects against solid objects over 1mm and water spray, suitable for indoor use.
- **Red Lens Colour:** Enhances visibility, ensuring alerts are noticeable.
- **Steady Light Effect:** Provides consistent visual signalling, ideal for continuous alerts.
- **Sound Level 88-92 dB:** Adjustable sound level to suit different environments and requirements.
- **Screw Mount Type:** Allows secure and easy installation.

RS PRO LED Horn-Beacon Combination, Red Lens

RS Stock No: 658-298



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO Horn-Beacon Combination is a versatile signalling device designed for industrial environments. It combines both visual and audible alerts, making it ideal for safety and warning applications. With its robust construction and reliable performance, it ensures effective communication in various settings.

General Specifications

Bulb Type	LED
Housing Colour	Grey
Lens Colour	Red
Light Effect	Steady
Mount Type	Screw
Number of Tones	1
Product Type	Horn-Beacon Combination
Sounder Type	Sounder Beacon

Electrical Specifications

Current Consumption	0.04 A
Current Type	AC
Maximum Supply Voltage	240 V ac

Mechanical Specifications

Housing Material	ABS
------------------	-----

Protection Category

IP Rating	IP43
-----------	------

Operation Environment Specifications

Maximum Operating Temperature	50 °C
Minimum Operating Temperature	-20 °C

Measurement Specifications

Maximum Sound Level	92 dB
Minimum Sound Level	88 dB

Approvals

Standards/Approvals	CE, EAC
---------------------	---------