


## FEATURES

- **High Shore A Hardness (90 to 95):** Ensures excellent wear resistance and durability in demanding environments
- **Wide Temperature Range (-20 °C to 140 °C):** Suitable for both high and low-temperature applications
- **Fluoroelastomer Material:** Offers superior chemical resistance, extending the lifespan of the seal
- **Precise Dimensions (126.59 mm ID, 133.65 mm OD, 3.53 mm Thickness):** Ensures a perfect fit for effective sealing
- **Black Colour:** Provides a professional appearance and easy identification

## RS PRO Shore A 90 to 95 O-Ring Seal, Black Fluoroelastomer

RS Stock No: 731-379



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO O-Ring Seal is designed for high-performance sealing applications. Made from durable fluoroelastomer materials, it is ideal for use in environments requiring chemical resistance and high-temperature stability. The O-Ring provides reliable sealing solutions for a variety of industrial applications.

## General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

## Mechanical Specifications

Inside Diameter	126.59 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	133.65 mm
Thickness	3.53 mm

## Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

## Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

