

## Features

- Manufactured from UL94HB flame-rated, UL-approved Nylon 612
- Resistant to ultraviolet (UV) radiation.
- Chemically resistant to substances such as zinc chloride, hydrocarbons, salts, bases, and acid rain.
- Suitable for applications in the solar industry, particularly for managing wiring on galvanised surfaces, and in environments requiring resistance to outdoor ageing and corrosion

## RS PRO Cable Ties

RS Stock No.: 0656031



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

This cable tie is designed for durability and reliability in demanding environments. Made from UL-approved, flame-rated nylon, it offers excellent resistance to UV exposure, chemicals, and harsh weather conditions. Ideal for solar industry applications, it provides secure fastening on galvanised surfaces while ensuring long-term performance against outdoor ageing and corrosion.

## General Specifications

|                               |   |
|-------------------------------|---|
| Series                        | Solar Industry  |
| Type                          | Non-Releasable  |
| Colour                        | Black   |
| Material                      | Nylon 612   |
| Finish                        | Smooth  |
| Application                   | Designed for quick installation and bundling of cables  |
| Resistant To                  | UV Resistant. Chemical Resistant (zinc chloride, hydrocarbons, salts, bases, acid rain, etc.) |
| UV Resistant                  | Yes   |
| Minimum Operating Temperature | Not specified   |
| Maximum Operating Temperature | Not specified   |
| Fire Behaviour                | Self-Extinguishing  |
| Quantity                      | 100   |

## Mechanical Specifications

|                  |       |
|------------------|-------|
| Length           | 368mm |
| Width            | 4.8mm |
| Tensile Strength | 222N  |

## Approvals

|               |                    |
|---------------|--------------------|
| Declarations  | RoHS, Halogen Free |
| Standards Met | UL                 |

