

# SAC-5P-M12MS/15,0-PUR/M12FS SH - Sensor/actuator cable



1530841

<https://www.phoenixcontact.com/in/products/1530841>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, PUR halogen-free, black-gray RAL 7021, shielded (Advanced Shielding Technology), Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: 15 m

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1530841                        |
| Packing unit                         | 5 pc                           |
| Minimum order quantity               | 5 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BF1                            |
| Product key                          | AF1CKA                         |
| GTIN                                 | 4017918990435                  |
| Weight per piece (including packing) | 729.2 g                        |
| Weight per piece (excluding packing) | 707 g                          |
| Customs tariff number                | 85444290                       |
| Country of origin                    | PL                             |

# SAC-5P-M12MS/15,0-PUR/M12FS SH - Sensor/actuator cable



1530841

<https://www.phoenixcontact.com/in/products/1530841>

## Technical data

### Product properties

|                      |                       |
|----------------------|-----------------------|
| Product type         | Sensor/actuator cable |
| Application          | Standard              |
| Number of positions  | 5                     |
| No. of cable outlets | 1                     |
| Shielded             | yes                   |
| Coding               | A                     |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Flammability rating according to UL 94 | HB                                          |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn                                        |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU                                         |
| Material for screw connection          | Zinc die-cast, nickel-plated                |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 48 V AC                    |
|                       | 60 V DC                    |
| Nominal current $I_N$ | 4 A                        |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | No |

### Connection data

#### Conductor connection

|                   |                        |
|-------------------|------------------------|
| Tightening torque | 0.4 Nm (M12 connector) |
|-------------------|------------------------|

### Connector

#### Connection 1

|      |                   |
|------|-------------------|
| Type | Plug straight M12 |
|------|-------------------|

# SAC-5P-M12MS/15,0-PUR/M12FS SH - Sensor/actuator cable



1530841

<https://www.phoenixcontact.com/in/products/1530841>

|                     |   |
|---------------------|---|
| Number of positions | 5 |
| Coding type         | A |

## Connection 2

|                     |                     |
|---------------------|---------------------|
| Type                | Socket straight M12 |
| Number of positions | 5                   |
| Coding type         | A                   |

## Cable/line

|              |      |
|--------------|------|
| Cable length | 15 m |
|--------------|------|

## PUR halogen-free black [PUR]

|                                               |                                                                                     |
|-----------------------------------------------|-------------------------------------------------------------------------------------|
| Dimensional drawing                           |  |
| Cable weight                                  | 43 kg/km                                                                            |
| UL AWM Style                                  | 20549 / 10493 (80°C/300 V)                                                          |
| Number of positions                           | 5                                                                                   |
| Shielded                                      | yes                                                                                 |
| Cable type                                    | PUR halogen-free black [PUR]                                                        |
| Conductor structure signal line               | 42x 0.10 mm                                                                         |
| AWG signal line                               | 22                                                                                  |
| Conductor cross section                       | 5x 0.34 mm <sup>2</sup> (Signal line)                                               |
| Wire diameter incl. insulation                | 1.27 mm ±0.02 mm (Signal line)                                                      |
| External cable diameter                       | 5.25 mm ±0.2 mm                                                                     |
| Outer sheath, material                        | PUR                                                                                 |
| External sheath, color                        | black-gray RAL 7021                                                                 |
| Conductor material                            | Bare Cu litz wires                                                                  |
| Material wire insulation                      | PP                                                                                  |
| Single wire, color                            | brown, white, blue, black, gray                                                     |
| Thickness, insulation                         | ≥ 0.21 mm                                                                           |
| Thickness, outer sheath                       | approx. 0.50 mm                                                                     |
| Overall twist                                 | 5 wires around filler to the core                                                   |
| Optical shield covering                       | 80 %                                                                                |
| Max. conductor resistance                     | max. 57 Ω/km (at 20 °C)                                                             |
| Insulation resistance                         | 70 GΩ*km (at 20 °C)                                                                 |
| Nominal voltage, cable                        | 300 V (at 20 °C)                                                                    |
| Test voltage Core/Core                        | 3000 V (at 20 °C)                                                                   |
| Smallest bending radius, fixed installation   | 26 mm                                                                               |
| Smallest bending radius, movable installation | 52 mm (up to +60 °C)                                                                |

# SAC-5P-M12MS/15,0-PUR/M12FS SH - Sensor/actuator cable



1530841

<https://www.phoenixcontact.com/in/products/1530841>

|                                 |                                                                                                                                                                                                                 |
|---------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Dynamic load capacity (bending) | Max. bending cycles: 10000000, Bending radius: 52 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup>                                                                          |
| Halogen-free                    | in accordance with DIN VDE 0472 part 815<br>in accordance with DIN EN 50267-2-1                                                                                                                                 |
| Flame resistance                | in accordance with UL 758/1581 FT2<br>DIN EN 60332-2-2 (20 s)                                                                                                                                                   |
| Resistance to oil               | in accordance with DIN EN 60811-2-1                                                                                                                                                                             |
| Other resistance                | Highly resistant to acids, alkaline solutions and solvents<br>hydrolysis and microbe resistant<br>Resistant to salt water<br>partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)<br>abrasion-resistant |
| Special properties              | Flexible cable conduit capable<br>Silicone-free<br>Free of substances which would hinder coating with paint or varnish<br>Low adhesion surface                                                                  |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation)<br>-25 °C ... 80 °C (Cable, flexible installation)                                                                                                                 |

## Environmental and real-life conditions

### Ambient conditions

|                                 |                                                                                                                                    |
|---------------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Degree of protection            | IP67                                                                                                                               |
| Ambient temperature (operation) | -25 °C ... 90 °C (Plug / socket)<br>-25 °C ... 80 °C (cable, fixed installation)<br>-5 °C ... 80 °C (Cable, flexible installation) |

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |

# SAC-5P-M12MS/15,0-PUR/M12FS SH - Sensor/actuator cable



1530841

<https://www.phoenixcontact.com/in/products/1530841>


## Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

# SAC-5P-M12MS/15,0-PUR/M12FS SH - Sensor/actuator cable



1530841

<https://www.phoenixcontact.com/in/products/1530841>

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

# SAC-5P-M12MS/15,0-PUR/M12FS SH - Sensor/actuator cable



1530841

<https://www.phoenixcontact.com/in/products/1530841>

Diagram




# SAC-5P-M12MS/15,0-PUR/M12FS SH - Sensor/actuator cable



1530841


<https://www.phoenixcontact.com/in/products/1530841>

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

Dimensional drawing



M12 x 1 socket, straight, shielded

# SAC-5P-M12MS/15,0-PUR/M12FS SH - Sensor/actuator cable



1530841

<https://www.phoenixcontact.com/in/products/1530841>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1530841>



### UL Listed

Approval ID: FILE E 221474

|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | 125 V                 | 4 A                   | -                 | -                           |



### cUL Listed

Approval ID: FILE E 221474

|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | 125 V                 | 4 A                   | -                 | -                           |



### EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

### cULus Listed

# SAC-5P-M12MS/15,0-PUR/M12FS SH - Sensor/actuator cable



1530841

<https://www.phoenixcontact.com/in/products/1530841>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27060311 |
| ECLASS-12.0 | 27060311 |
| ECLASS-13.0 | 27060311 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# SAC-5P-M12MS/15,0-PUR/M12FS SH - Sensor/actuator cable



1530841

<https://www.phoenixcontact.com/in/products/1530841>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.  
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420  
[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)