

Product data sheet

Specifications



Repacked, modular bell, Resi9 XP SO, 80dB, 230VAC

R9PCBSW



This repacked option saves 0.485 over the standard condition

Main

range of product	Resi9
Product name	Resi9 XP SO
Product or component type	Bell

Complementary

[Ue] rated operational voltage	230 V AC 50/60 Hz
Power consumption in VA	5.5 VA
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	2
Height	81 mm
Width	18 mm
Depth	65 mm
Product weight	59 g
Colour	White (RAL 9003)
Connections - terminals	Tunnel type terminal - 1...4 mm ² - rigid Tunnel type terminal - 1...4 mm ² - flexible Tunnel type terminal - 1...4 mm ² - flexible with ferrule
Tightening torque	0.8 N.m
Market segment	Residential

Environment

Standards	EN/IEC 62080
Quality labels	IMQ
Noise level	80 dB
Type of sound	Bell
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...70 °C

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of Units in Package 1	1
Package 1 Height	1.800 cm
Package 1 Width	6.600 cm
Package 1 Length	8.300 cm
Package 1 Weight	62.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	24
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.676 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.5 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

6edbd8bf-8086-4f8e-a012-80f9e4a1db80

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins