



OPERATION INSTRUCTIONS

© Panduit Corp. 2013


**TOOL MAINTENANCE**

TO INHIBIT CORROSION AND MAINTAIN PERFORMANCE OF THE TOOL, KEEP THE METAL SURFACES COATED WITH A LIGHT OIL (WD-40® OR EQUIVALENT).

NOTE: This precision tool has been engineered and designed for use with Panduit Pan-Steel Stainless Steel Ties. It is not intended for other uses such as cutting or tensioning other types of fastening devices.

**OPERATING INSTRUCTIONS**

1. Loop tie around bundle and insert tip through head. Pull tie up snug on bundle by hand.
2. Place tool on tie as shown.
3. Squeeze handles as many times as necessary to tighten tie to the desired tension.
4. While maintaining final handle pressure from Step 3, rotate tool 1/4 to 1/2 turn until excess tail is cut off. Remove cut-off portion from tool.





FOR INSTALLING:
Pan-Steel Stainless Steel Ties of
Standard, Light-Heavy, Heavy and
Extra-Heavy cross sections.

Part No. ST2MT
STAINLESS STEEL CLAMP
INSTALLATION TOOL

MADE IN USA

NOT INTENDED FOR MEDICAL USE.
User is responsible to determine suitability
of product for intended use.

REPLACEMENT KIT: (SOLD SEPARATELY)
KT2MG - Gripper Replacement Kit



For Technical Support:
888-506-5400, ext. 83255

Website: www.panduit.com
E-mail: techsupport@panduit.com