

www.vishay.com

Vishay Spectrol

## 1/2" (12.7 mm) Conductive Plastic and Cermet Potentiometer



#### **FEATURES**

- · Robust construction
- High rotational life (50 000 cycles)




- Up to three sections PC support plates
- Rotary switches and solder lugs terminals available
- Tests according to CECC 41000 or IEC 60393-1
- Material categorization: for definitions of compliance please see <a href="https://www.vishay.com/doc?99912"><u>www.vishay.com/doc?99912</u></a>

### **148 FEATURES**

- · Conductive plastic element
- · Quiet electrical output

### **149 FEATURES**

- · Cermet element
- Low temperature coefficient (± 150 ppm/°C)





# Vishay Spectrol

ELECTRICAL SPEC	ELECTRICAL SPECIFICATIONS								
PARAMETER		148	149						
Decistores Dongs	Linear	1 kΩ to 1 MΩ	100 $\Omega$ to 2 M $\Omega$						
Resistance Range	Non-Linear	500 $\Omega$ to 500 k $\Omega$	250 $\Omega$ to 1 M $\Omega$						
Tolerance	Linear	10 %	10 %						
Tolerance	Non-Linear	20 % on request 10 %	10 %						
Linearity (Typical)		± 5 % ind	ependent						
End Resistance		4 Ω maximu	m each end						
Power Rating		0.5 W at 70 °C 0 W at 120 °C	1 W at 70 °C 0 W at 150 °C						
-		Non-Linear or PC n	nount, derate 50 %						
Circuit Diagram  (1)  b → cw (2)									
Effective Rotation		$270^{\circ} \pm 10^{\circ}$ without rotary switch $240^{\circ} \pm 10^{\circ}$ with rotary switch							
Contact Resistance Variati	on (Typical)	1.5 % of total resistance	3 % of total resistance						
Maximum Continuous Wor	king Voltage	350 V <sub>AC</sub> across end terminals, but within power rating							
Dielectric Withstanding Vo	ltage	e Sea level -750 V <sub>AC</sub>							

MECHANICAL S	PECIFICATIONS				
Mechanical Travel		300° ± 5°			
Operating Torque (Typical)		Single section 0.2 oz. to 3.0 oz in dual or triple section 0.3 ozinch to 4.5 ozinch			
End Stop Torque	Bushing A and B	2.1 lb-inch max.			
End Stop Torque	Bushing F	6.8 lb-inch max.			
	Single	0.19 oz.			
Weight (approx.)	Dual	0.27 oz.			
	Triple	0.35 oz.			
Terminals	Electrical Elements	e3: Pure Sn			
Terriniais	Switch Elements	e4: Gold plated			

ENVIRONMENTAL SPECIFICATIONS								
	148	149						
Operating Temperature	-40 °C to +125 °C	-40 °C to +125 °C						
Storage Temperature	-55 °C to +125 °C	-55 °C to +125 °C						
Temperature Cycling (5 Cycles)	-40 °C to +125 °C (4 % ΔR <sub>T</sub> )	-40 °C to +125 °C (3 % ΔR <sub>T</sub> )						
Load Life (1000 h Rated Load at 70 °C)	10 % ΔR <sub>T</sub> 5 % ΔR <sub>T</sub>							
Mechanical Endurance	50 000	cycles						
TCR (Typical)	± 500 ppm/°C	± 150 ppm/°C						
Sealing	IP64							

### Note

• Nothing stated herein shall be construed as a guarantee of quality or durability.




## Vishay Spectrol

### **LOCATING PEGS** (anti-rotation lug)

The locating peg is provided by a plate mounted on the bushing and positioned by the module sides. Four set positions are available, clock face orientation: 12, 3, 6, 9.


All 148, 149 bushings have a double flat. When panel mounting holes have been punched accordingly, an anti-rotation lug is not necessary.



CODE	VERSION	BUSHING A, B	BUSHING F	EFFECTIVE HIGH PEG	
۸	Ø d mm	2	2	0.7	
Α	L mm	6.2	6.2	-	
В	Ø d mm	2	2	0.7	
ь	L mm	7.75	7.75	-	
С	Ø d mm	-	3.5	1.1	
C	L mm	-	13.5	-	

Locating pegs are supplied in separate bags with nuts and washers

### **RSID OPTION: ROTARY SWITCH MODULES**



- Rotary switches
- Current up to 2 A
- SPDT: Single pole, changeover switch in CCW position 3 pins
- Sealing IP60

## MODULES: RS ON/OFF SWITCH RSI CHANGEOVER SWITCH

The position of each module is free.

RS and RSI rotary switches are housed in a standard 148, 149 module size 12.7 mm x 12.7 mm x 5.08 mm (0.5" x 0.5" x 0.2"). They have the same terminal styles as the assembled electrical modules.

An assembly can comprise 1 or more switch modules.

Switch actuation is described as seen from the shaft end. D: means actuation in maximum CCW position

The switch actuation travel is 25° with a total mechanical travel of 300°  $\pm\,5^\circ$  and electrical travel of electrical modules is 238°  $\pm\,10^\circ.$ 

### **RSID Single Pole CHANGEOVER**

In full CCW position, the contact is made between 3 and 2 and open between 3 and 1. Switch actuation (CW direction) reverses these positions.

SWITCH SPE	SWITCH SPECIFICATIONS								
Switching Por	wer Maximum	62.5 VA v 15 VA =							
Switching Current Maximum  0.25 A 250 V v  0.5 A 30 V =									
Maximum Cu	rrent Through Element	2 A							
Contact Resis	stance	100 mΩ							
Dielectric	Terminal to Terminal	1000 V <sub>RMS</sub>							
Strength	Terminal to Bushing	2000 V <sub>RMS</sub>							
Maximum Vol	tage Operation	250 V v 30 V =							
Insulation Resistance Between Contacts $10^6  \mathrm{M}\Omega$									
Life at P <sub>max.</sub>	Life at P <sub>max.</sub>								
Minimal Trave	el .	25°							
Operating Ter	mperature	-40 °C to +85 °C							


#### **ELECTRICAL DIAGRAM**

### RSID CCW POSITION




### Note

(1) Common







BUSHING			
	Ø	L	OLD CODES
Α	1/4"	1/4"	N
В	1/4"	3/8"	J
F	3/8"	3/8"	G

LEAD	LEADS											
	TYPE	PIN SPACING	SPACE BETWEEN MODULES	OLD CODES								
X10	DOD :	2.54 mm	n/a	-								
X13	PCB pins	(0.100")	7.62 mm (0.300")	Р								
A10	PCB pins and	2.54 mm	n/a	_								
A13	support plates	(0.100")	7.62 mm (0.300")	E								
Y00		4.65 mm	n/a									
Y03	Sold, lugs	(0.183")	7.62 mm (0.300")	S								

SHAFT									
	Ø	L	OLD CODES						
BB	1/8"	1/2"	32						
BG	1/8"	5/8"	40						
ВН	1/8"	3/4"	48						
BJ	1/8"	7/8"	56						
GB	1/4"	1/2"	32						
GG	1/4"	5/8"	40						
GH	1/4"	3/4"	48						
GJ	1/4"	7/8"	56						
GL	1/4"	1"	64						
GN	1/4"	1 1/4"	80						

PART NUMBER DESCRIPTION (for information only)														
148	1	0	F	0	GJ	S	X10	BO50	10K	10 %	Α			е3
MODEL	MODLUES	SWITCH	BUSHING	LOCATING PEG	SHAFT	SHAFT	LEADS	PACK.	VALUE	TOL.	TAPER	SPECIAL	SPECIAL	LEAD FINISH



### **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000