

# Eaton 192316

Catalog Number: 192316

Eaton Moeller series NZM - Molded Case Circuit Breaker. NZM3 PXR25, class 1, 250A, 4p, variable, earth-fault protection, ARMS and zone selectivity, withdrawable unit, S, 3

## General specifications



Product Name	Catalog Number
Eaton Moeller series NZM molded case circuit breaker electronic	192316
	EAN
	4015081928675
Product Length/Depth	Product Height
346 mm	260 mm
Product Width	Product Weight
230 mm	24.45 kg
Compliances	Certifications
RoHS conform	IEC
	IEC/EN 60947

## Product specifications

### Type

Circuit breaker

### Special features

LSIG overload protection  
and delayed and non-  
delayed short-circuit  
protective device, earth-fault  
protection  
Class 1 energy  
measurement, r.m.s. value  
measurement, and "thermal  
memory"  
USB interface for  
configuration and test  
function with Power Xpert  
Protection Manager  
software  
Zone selectivity ZSI  
Maintenance Mode ARMS  
Interface module in  
equipment supplied.  
Optionally communication-  
capable with internal  
Modbus RTU module or  
CAM  
Maximum back-up fuse, if  
the expected short-circuit  
currents at the installation  
location exceed the  
switching capacity of the  
circuit breaker (Rated short-  
circuit breaking capacity  $I_{cn}$ )  
Rated current = rated  
uninterrupted current: 250 A  
Terminal capacity hint: Up to  
240 mm<sup>2</sup> can be connected  
depending on the cable  
manufacturer.

### Application

Use in unearthed supply systems at 690 V

### Amperage Rating

250 A

### Voltage rating

## Resources

### Brochures

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

### Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

### Characteristic curve

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-022.eps](#)

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-026.eps](#)

### Drawings

[eaton-circuit-breaker-nzm-mccb-dimensions-021.eps](#)

[eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps](#)

### Installation instructions

[eaton-circuit-breaker-basic-unit-bg3-il012100zu.pdf](#)

### Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

### mCAD model

[DA-CD-nzm3\\_3p](#)

[DA-CS-nzm3\\_3p](#)

### Technical data sheets

[eaton-nzm-technical-information-sheet](#)

690 V - 690 V

#### Circuit breaker frame type

NZM3

#### Features

Motor drive optional

Protection unit

#### Accessories required

NZM3-4-XAVS

#### 10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

#### 10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

#### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

#### 10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

#### 10.2.2 Corrosion resistance

Meets the product standard's requirements.

#### 10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

#### 10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

#### 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

#### 10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

#### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.7 Inscriptions

Meets the product standard's requirements.

#### 10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

#### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### Pollution degree

3

#### Mounting Method

Withdrawable

Built-in device slide-in technique (withdrawable)

#### Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

#### Equipment heat dissipation, current-dependent

28.13 W

#### Utilization category

A (IEC/EN 60947-2)

#### Isolation

300 V AC (between the auxiliary contacts)

500 V AC (between auxiliary contacts and main contacts)

#### Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

40 °C

Number of auxiliary contacts (change-over contacts)

0

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

0

Protection against direct contact

Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part

110

Degree of protection

IP20 (basic degree of protection, in the operating controls area)

IP20

Direction of incoming supply

As required

Electrical connection type of main circuit

Other

Current rating of neutral conductor

0 - 60% - 100% of phase conductor

Lifespan, mechanical

15000 operations

Overvoltage category

III

Degree of protection (IP), front side

IP66 (with door coupling rotary handle)

IP40 (with insulating surround)

Degree of protection (terminations)

IP10 (tunnel terminal)

IP00 (terminations, phase isolator and strip terminal)

Number of poles

Four-pole

Terminal capacity (copper strip)

Max. 8 segments of 24 mm x 1 mm (2x) at box terminal

Min. 6 segments of 16 mm x 0.8 mm at rear-side connection  
(punched)

Max. 10 segments of 24 mm x 1 mm + 5 segments of 24 mm x 1  
mm

10 segments of 50 mm x 1 mm (2x) at rear-side width extension

Max. 10 segments of 32 mm x 1 mm + 5 segments of 32 mm x 1  
mm at rear-side connection (punched)

Min. 6 segments of 16 mm x 0.8 mm at box terminal

#### Lifespan, electrical

5000 operations at 415 V AC-1

3000 operations at 690 V AC-1

5000 operations at 400 V AC-1

#### Functions

Zone selectivity

ARMS maintenance mode

Integrated earth fault protection

Systems, cable, selectivity and generator protection

Earth-fault protection

#### Earth-fault current setting ( $I_g$ ) - max

250 x  $I_n$

#### Shock resistance

20 g (half-sinusoidal shock 20 ms)

#### Earth-fault current setting ( $I_g$ ) - min

50 x  $I_n$

#### Position of connection for main current circuit

Connection at separate chassis part

#### Rated operational current for specified heat dissipation ( $I_n$ )

250 A

#### Release system

Electronic release

#### Short-circuit total breaktime

< 10 ms

#### Rated short-time withstand current ( $t = 0.3$ s)

3.3 kA

#### Rated short-time withstand current ( $t = 1$ s)

3.3 kA

#### Short-circuit release delayed setting - max

2500 A

#### Short-circuit release delayed setting - min

200 A

#### Short-circuit release non-delayed setting - max

4500 A

#### Short-circuit release non-delayed setting - min

500 A

#### Terminal capacity (control cable)

0.75 mm<sup>2</sup> - 1.5 mm<sup>2</sup> (2x)

0.75 mm<sup>2</sup> - 2.5 mm<sup>2</sup> (1x)

#### Terminal capacity (copper busbar)

M10 at rear-side screw connection

Max. 10 mm x 50 mm (2x) at rear-side width extension

Max. 30 mm x 10 mm + 30 mm x 5 mm direct at switch rear-side connection

Min. 20 mm x 5 mm direct at switch rear-side connection

#### Terminal capacity (copper solid conductor/cable)

16 mm<sup>2</sup> (2x) direct at switch rear-side connection

300 mm<sup>2</sup> (2x) at rear-side width extension

16 mm<sup>2</sup> (2x) at box terminal

16 mm<sup>2</sup> (1x) at tunnel terminal

16 mm<sup>2</sup> (1x) direct at switch rear-side connection

#### Terminal capacity (aluminum solid conductor/cable)

16 mm<sup>2</sup> (1x) at tunnel terminal

#### Terminal capacity (copper stranded conductor/cable)

25 mm<sup>2</sup> - 240 mm<sup>2</sup> (1x) direct at switch rear-side connection

25 mm<sup>2</sup> - 240 mm<sup>2</sup> (2x) direct at switch rear-side connection

35 mm<sup>2</sup> - 240 mm<sup>2</sup> (1x) at box terminal

16 mm<sup>2</sup> - 185 mm<sup>2</sup> (1x) at 1-hole tunnel terminal

25 mm<sup>2</sup> - 120 mm<sup>2</sup> (2x) at box terminal

#### Terminal capacity (aluminum stranded conductor/cable)

25 mm<sup>2</sup> - 185 mm<sup>2</sup> (1x) at tunnel terminal

50 mm<sup>2</sup> - 240 mm<sup>2</sup> (1x) at 2-hole tunnel terminal

50 mm<sup>2</sup> - 240 mm<sup>2</sup> (2x) at 2-hole tunnel terminal

#### Handle type

Rocker lever

#### Short delay current setting (I<sub>sd</sub>) - max

10 A

#### Short delay current setting (I<sub>sd</sub>) - min

2 A

#### Instantaneous current setting (I<sub>i</sub>) - max

18 A

#### Instantaneous current setting (I<sub>i</sub>) - min

2 A

Number of operations per hour - max

60

Overload current setting (Ir) - max

250 A

Overload current setting (Ir) - min

100 A

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 230 V, 50/60 Hz

100 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 400/415 V, 50/60 Hz

70 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 440 V, 50/60 Hz

65 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 525 V, 50/60 Hz

18 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 690 V, 50/60 Hz

6 kA

Rated short-circuit making capacity Icm at 400/415 V, 50/60 Hz

154 kA

Rated short-circuit making capacity Icm at 440 V, 50/60 Hz

143 kA

Rated short-circuit making capacity Icm at 525 V, 50/60 Hz

80 kA

Rated short-circuit making capacity Icm at 690 V, 50/60 Hz

50 kA

Standard terminals

Screw terminal

Optional terminals

Box terminal. Connection on rear. Tunnel terminal

Rated short-circuit making capacity Icm at 240 V, 50/60 Hz

220 kA

Rated impulse withstand voltage (Uimp) at auxiliary contacts

6000 V

Rated impulse withstand voltage (Uimp) at main contacts

8000 V



Rated insulation voltage (Ui)  
690 V AC



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)