

**FAG****X-life****WS22209-E1-XL-2RSR** **Spherical Roller Bearing**

Sealed spherical roller bearings WS222...-E1, lip seals on both sides, for continuous casting machines

Technical information**Your current product variant**

Design	E1	without central rip
Bore type	Z	Cylindrical
Cage	JPA	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication feature	Standard	
Sealing	2RSR	Seals on both sides, normal temperature
Sealing - excess width	WS	Sealing - excess width

Main Dimensions & Performance Data

d	45 mm	Bore diameter
D	85 mm	Outside diameter
B	28 mm	Width
C _r	104,000 N	Basic dynamic load rating, radial
C _{0r}	99,000 N	Basic static load rating, radial
C _{ur}	13,000 N	Fatigue load limit, radial
n _G	2,550 1/min	Limiting speed
≈m	0.645 kg	Weight



Mounting dimensions

d _{a min}	51.4 mm	Minimum diameter shaft shoulder
D _{a max}	78 mm	Maximum diameter of housing shoulder
r _{a max}	1 mm	Maximum recess radius

Dimensions

r _{min}	1.1 mm	Minimum chamfer dimension
D ₁	77.8 mm	Bore diameter outer ring
d ₂	51.4 mm	Raceway diameter of the inner ring
d _s	3.2 mm	Diameter lubrication hole
n _s	4.8 mm	Width of lubricating groove

Temperature range









T _{min}	-30 °C	Operating temperature min.
T _{max}	100 °C	Operating temperature max.

Calculation factors

e	0.25	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	2.74	Dynamic axial load factor
Y ₂	4.08	Dynamic axial load factor
Y ₀	2.68	Static axial load factor



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Lifetime lubrication, freedom from maintenance
-  Grease Lubrication
-  Sealed on both sides
-  Static angular error and misalignment
-  Dynamic angular error and misalignment