

Dust Extractor XGT®

VC001GL

40Vmax • 230 mbar • 8 L • L

XGT® Battery powered Wet/dry dust extractor for cleaning.

A versatile wet/dry dust extractor that runs on with XGT® battery. The batteries can be connected in parallel. It Matches filter class 'L'. Tank capacity is 8 L which enables continuous cleaning work.



Technical specifications

Vacuum hose length	1,7 m
Vacuum hose diameter	32 mm
Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Air volume	3,2 m³/min
Max. sealed suction	230 mbar
Suction power	310 W
Continuous Use XGT® 40V Max / 5.0 Ah X2	28 - 220 min
Tank Capacity for Dust	8 L
Tank Capacity for Liquids	6 L
Product net weight	7,7 kg
Sound Pressure Level (L _{pA})	≤ 70 dB(A)
Noise Uncertainty (K Factor)	2,5 dB(A)
Tool weight with battery	8,1 - 11,2 kg
Product Dimensions (L x W x H):	366 x 334 x 425

User benefits

- Quiet operation for operator comfort
- For both wet and dry vacuum cleaning
- Flat top design for space saving in storage
- Carry handle for easy transportation
- Approved for Dust Class L in accordance with the EU standard
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitaauk.com



Related products

■ Optional AC

191V67-2

Water Filter Set



■ Other

User manual

Parts drawing