


FEATURES

- **Annealed Copper Conductor:** Provides superior conductivity and durability
- **Polyvinyl Chloride Jacket:** Offers protection against environmental factors
- **3-Core Design:** Facilitates versatile electrical connections
- **Operating Temperature Range -15 °C to 90 °C:** Suitable for diverse environments
- **Voltage Rating 500 V:** Supports high voltage applications
- **Plain Conductor Type:** Ensures consistent electrical performance
- **White Jacket Colour:** Easy identification and aesthetic integration

RS PRO 2.5 mm² Flexible Cable, 100 m

RS Stock No: 606-117



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial and commercial settings. With a conductor made from annealed copper, it ensures excellent conductivity and durability. The cable is suitable for installations requiring flexibility and robust performance.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	White
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	2.5 mm ²
Cable Length	100 m
Core Strands	50/0.25
Jacket Material	Polyvinyl Chloride
Number of Cores	3
Outside Diameter	11.4 mm

Operation Environment Specifications

Maximum Operating Temperature	90 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

Electrical Specifications

Voltage	500 V
---------	-------