

1806024

https://www.phoenixcontact.com/gb/products/1806024

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, Range of articles: SUNCLIX, color: black, number of positions: 1, min. conductor cross section: 6 mm², Connection method: Crimp, Contact connection type: Socket, cable length: 350

Commercial data

Item number	1806024
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	ABLBAA
Product key	ABLBAA
GTIN	4046356688932
Weight per piece (including packing)	31.32 g
Weight per piece (excluding packing)	30.865 g
Customs tariff number	85359000
Country of origin	DE



1806024

https://www.phoenixcontact.com/gb/products/1806024

Technical data

Notes

Safety note

Safety note

- WARNING: Commission properly functioning products only.
 The products must be regularly inspected for damage.
 Decommission defective products immediately. Replace damaged products. Repairs are not possible.
- WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.

WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.

- The products are suitable for applications in plant, controller, and electrical device engineering.
- Assembled products may not be manipulated or improperly opened.
- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).
- When using the product in direct connection with third-party manufacturers, the user is responsible.
- For operating voltages > 50 V AC, conductive connector housings must be grounded
- Ensure that the protective or functional ground has been properly connected.
- Observe the corresponding technical data. You will find information:
- o On the product
- o On the packing label
- o In the supplied documentation
- o Online at phoenixcontact.com/products under the product
- The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.
- Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at phoenixcontact.com/products
- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).
- Operate the connector only when it is fully plugged in and interlocked.
- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.



1806024

https://www.phoenixcontact.com/gb/products/1806024

Color of the housing part

Material Housing

Material Contact carrier

	Observe the minimum bending radius of the cable. Lay the cable without twisting it.
Product properties	
Product type	Panel feed-through
Product family	SUNCLIX
Number of positions	1
Insulation characteristics	
Protection class	II
Degree of pollution	2
Connection data	
Conductor connection	
Tightening torque	1.8 Nm ±0.1 Nm
Dimensions	
Dimensional drawing	43,2 9 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0
Width	18.6 mm
Height	18.6 mm
Length	43.2 mm
Electrical properties	
Rated voltage (III/2)	1000 V
Rated surge voltage (III/2)	12 kV
Rated current (6.0 mm²)	40 A
Contact resistance	0.45 mΩ
Contact resistance	≤ 0.45 m Ω (when plugged in (without cable))
Mechanical properties	
Mechanical data	
Insertion/withdrawal cycles	100
Insertion force	45 N ±10 N
Withdrawal force	250 N ±50 N (when locked)
Material specifications	
Color	black

black PPE

PPE



1806024

https://www.phoenixcontact.com/gb/products/1806024

Material Contact	Cu
Material Seal	EPDM
Material Contact surface	Ag
Material	Silopren LSR 2660 (O-ring)
Flammability rating according to UL 94	V0
Insulating material group	III
Insulating material	mPPE
Contact surface	Silver Ag
Cable seal material	Elastosil LR 3065/50
Outer sheath, material	PE-X

Cable/line

Cable length	350 mm
Cable type	Railway cable
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	84x0.3
Cable type	Railway cable Radox GKW-S
Cable structure	tin-plated, fine-wired, IEC 60228 Class 5
External cable diameter	5.40 mm ±0.15 mm
	5.10 mm 4.95 mm 5.25 mm ±0.15 mm
Outer sheath, material	PE-X
External sheath, color	black
Single wire, material	Cu
Single wire, cross section	6 mm²
Cable cross section	6 mm²
Smallest bending radius, fixed installation	10.2 mm (2x Ø)
Smallest bending radius, movable installation	15.3 mm (3x Ø)
Cable pull-out force	> 80 N
Halogen-free	yes
Resistance to oil	yes
Flame resistance	yes

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP66/IP68 (2 m / 24 h)
Degree of protection (not plugged in)	IP20
Degree of protection	IP66/IP68 (2 m / 24 h)
Ambient temperature (operation)	-40 °C 85 °C
Ambient temperature (assembly)	-25 °C 50 °C
Resistance to oil	yes

Standards and regulations

Flame resistance	yes
Resistance to oil	yes





1806024

https://www.phoenixcontact.com/gb/products/1806024

Drawings

Dimensional drawing






Dimension x = cable length c: panel thickness - plastic: 2 - 6 mm; metal: 2 - 5 mm



1806024

https://www.phoenixcontact.com/gb/products/1806024

Dimensional drawing



a: anti-rotation protection

b: coding

c: panel thickness - plastic: 2 - 6 mm; metal: 2 - 5 mm



1806024

https://www.phoenixcontact.com/gb/products/1806024

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/gb/products/1806024



TÜV Rheinland

Approval ID: R 60165003-0001



1806024

https://www.phoenixcontact.com/gb/products/1806024

Classifications

ECLASS		
	ECLASS-13.0	27440107
ETIM		
	ETIM 9.0	EC002635
U	NSPSC	



1806024

https://www.phoenixcontact.com/gb/products/1806024

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	Triphenyl phosphate(CAS: 115-86-6)
SCIP	101c270d-18d6-450a-8d93-c6430472cbe7

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

PHOENIX CONTACT Ltd Halesfield 13, Telford Shropshire, TF7 4PG 01952 681700 info@phoenixcontact.co.uk