




tesa® 50575

Product Information



Very strong 80µm aluminium tape with and without liner (PV1 and PV0)

Product Description

tesa® 50575 is a very strong aluminium tape based on a 80µm aluminium foil and an acrylic adhesive. tesa® 50575 has a high tensile strength and is mainly used in the appliance industry but also for a wide range of other applications.

Features:

- good adhesion
- mechanical resistance
- moisture resistant
- vapour tight
- flame retardant
- oil & acid resistant
- high thermal conductivity
- ageing resistant
- heat and light reflective
- resistant to strong acids and base solutions
- available without liner (PV0) and with liner (PV1)
- tesa® 50575 is certified by AREVA according to requirements of the Siemens AG standard TLV 9027/01/06 for nuclear power station: total halogen content < 1000 ppm total sulphur content <1000 ppm

Application Fields

- Masking during paint stripping
- Mounting of refrigerator coils
- General purpose temperature insulation
- Sealing of ducts
- Masking, protecting, repairing, closing .

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

• Backing material	aluminium foil	• Colour of liner	white
• Type of adhesive	acrylic	• Thickness of liner	65 µm
• Type of liner	paper	• Thickness of tape	_NULL µm
• Total thickness	120 µm		



tesa[®] 50575

Product Information

Properties/Performance Values

- | | | | |
|-------------------------------|------------|-------------------------------|--------|
| • Elongation at break | 5 % | • Hand tearability | good |
| • Tensile strength | 65 N/cm | • Operation temperature from | -40 °C |
| • Backing appearance (visual) | reflective | • Operation temperature up to | 160 °C |

Adhesion to Values

- | | |
|---------|--------|
| • steel | 4 N/cm |
|---------|--------|

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

For latest information on this product please visit <http://l.tesa.com/?ip=50575>