

2-160983-1 ✓ ACTIVE

AMP-TY


TE Internal #: 2-160983-1

Standard Cable Tie, Bag, 123.65 lbf Tensile Strength, 550 Newton Tensile Strength, 365 mm [14.4 in] Length, 7.8 mm [.307 in] Width, Natural

[View on TE.com >](#)



Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**

Packaging Method: **Bag**

Tensile Strength: **550 Newton**

Product Length: **365 mm [14.4 in]**

Features

Product Type Features

Cable Tie Style	Standard
Tensile Strength	550 Newton

Body Features

Primary Product Color	Natural
Primary Product Material	Polyamide 6.6 GF

Dimensions

Compatible Cable Bundle Diameter Range	100 mm[3.93 in]
Product Length	365 mm[14.4 in]
Product Width	7.8 mm[.307 in]
Product Thickness	1.8 mm[.07 in]

Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)

Candidate List Declared Against: JUNE 2024 (241)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # EC6474-000
13611420



TE Part # EC6495-000
13611441



TE Part # EC6540-000
13611921



TE Part # EC6545-000
13611926



TE Part # EC6547-000
13611928




TE Part # EC6551-000
13611932




TE Part # EC6460-000
13611406



TE Part # EC6525-000
13611906



Customers Also Bought



Documents

Product Drawings

CABLE TY 365X7.8 NAT

English

Datasheets & Catalog Pages

Connectivity Solutions for Industrial Applications

English

CABLE TIES

English

2-160983-1

Standard Cable Tie, Bag, 123.65 lbf Tensile Strength, 550 Newton Tensile Strength,
365 mm [14.4 in] Length, 7.8 mm [.307 in] Width, Natural

