

Product data sheet

Specifications



Repacked socket-outlet, Odace,
combi flush pin earth, 2P + E + USB
C, anthracite

S540089W



This repacked option saves 0.292 over the
standard condition

Main

Range	Odace
Product or component type	USB charger + socket-outlet
Colour tint	Anthracite

Complementary

Device presentation	Mechanism with fixing frame
Device mounting	Flush
Type of USB power supply	USB type C
Outlet poles configuration	2P + E
Outlet standard description	Pin earth
Outlet standard deviation	French
Socket number	1
Rated current	16 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50 Hz
Integrated connection type	1 USB type C 5 V DC, maximum load current: 2.4 A 1 socket-outlet 250 V AC, maximum load current: 16 A
Max output power on one port	10.5 W
fixing mode	By screws
Surface finish	Matt
Wire stripping length	12 mm
Height	71 mm
Width	71 mm
Depth	42.7 mm
Embedding depth	26.7 mm
Main colour tint	Anthracite

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	8.500 cm
Package 1 Length	13.000 cm
Package 1 Weight	75.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	13.500 cm
Package 2 Width	10.500 cm
Package 2 Length	27.500 cm
Package 2 Weight	450.000 g
Unit Type of Package 3	S04
Number of Units in Package 3	70
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	7.028 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.3 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

877db2a3-bca0-49d1-8140-447880b153d6

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins