




ENGLISH

Datasheet

Stock No: 510-333

# RS Pro Raised V bending tool for 3000lbs press



## Product Details

### Raised V Bending Tool

"V" bending jaws for use with the 3000 lb press, for the creation of bends of up to 90° in small boxes, brackets, etc. The raised base allows return folds to be made close together. Five blades are supplied of lengths 50 mm, 75 mm, 100 mm, 125 mm and 150 mm. Maximum bending capacity is 2.5 mm aluminium and 1.6 mm mild steel.

Production Tooling

## Specifications

Cutting Capacity	2.5 mm Aluminium; 1.6 mm Mild Steel
------------------	-------------------------------------