

Impact Wrench XGT®

TW002G

40Vmax, 1/2", 1 700 Nm, 0 – 1 800 min⁻¹

Model TW002G is a impact wrench powered by a 40Vmax XGT® Li-Ion battery. The tip shape of the anvil has been changed to a 12.7mm (1/2") square drive

Suitable for tasks such as chassis maintenance and construction site work. Driving shank 12.7mm (1/2") Square, C ring (without hole). Max fastening/Nut-busting torque: 1,700 / 2,200 Nm. 4 stage impact power selection. Automatic impact stop system in forward/reverse rotation. Trigger switch variable speed control + full speed.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Brushless Motor	✓
No load speed	0 - 850 / 900 / 1000 / 1800 min ⁻¹
Max Fastening Torque Impact Drill	280 / 630 / 1100 / 1700 Nm
Nut-busting torque	2200 Nm
Tightening Capacity Standard Bolt	M12 - M36
Tightening Capacity High Tensile Bolt	M10 - M27
Impacts per Minute (IPM)	0 - 1700 / 1800 / 2000 / 2400 min ⁻¹
Drive Square	1/2 "
Sound Power Level (L _{WA})	103 dB(A)
Sound Pressure Level (L _{pA})	95 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)

User benefits

- Brushless maintenance-free and long-life motor
- 3 modes of reaction time for automatic stop available both in forward and reverse rotation modes
- Electronic 4 stage impact power selection for added versatility
- Reverse rotation Auto Stop mode stops after the bolt/nut loosened enough
- Ergonomic soft grip handle provides increased comfort
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing