




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Wire**

Number of Positions: **2**

Number of Rows: **1**

Features

Product Type Features

Mixed & Hybrid Header	No
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Wire
Header Type	Fully Shrouded
Sealable	No
Connector Product Type	Connector Assembly

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	2
Number of Rows	1

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Size	1mm
--------------	-----



Contact Mating Area Plating Material	Tin (Sn)
Termination Features	
Termination Method to PCB	Through Hole - Solder
Mechanical Attachment	
Mating Alignment	With
Housing Features	
Centerline (Pitch)	5 mm
Usage Conditions	
Operating Temperature Range	-30 – 80 °C[-22 – 176 °F]
Other	
Interface Number	6098-2220, 90980-11987

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 1123900-1
FPC CONN.2P UNSEALED TAB
CONT.

Also in the Series | Multilock Connector System



Automotive Connector Caps & Covers
(6)



Automotive Headers(77)



Automotive Housings(166)




Automotive Terminals(84)



Insertion & Extraction Tools(6)




Other Automotive Connector
Accessories(6)



PCB Headers & Receptacles(77)



Rectangular Power Connectors(6)



Wire-to-Board Headers & Receptacles
(75)

Customers Also Bought





TE Part #1318382-8
025 16POS CAP ASSY H SELECTIVE-TIN



TE Part #CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM, HOUSING



TE Part #2040009-1
0.50/1.0 SEALED WIRE COVER ASSY 60POS



TE Part #174327-1
SCREW LOCK (M-2.6)



TE Part #353840-1
SEAT BELT FPC PLATE



TE Part #3-5178093-1
040/070 HYBRID CAP ASSY 38P



TE Part #2-5353016-1
040 III HD 105POS CAP ASSY H RND

Documents

- Product Drawings

FPC CONN.2P UNSEALED CAP ASSY

English

FPC CONN.2P UNSEALED CAP ASSY

English

FPC CONN.2P UNSEALED CAP ASSY

Japanese

- CAD Files

Customer View Model

ENG_CVM_CVM_1123899-1_E.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1123899-1_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1123899-1_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

- Product Specifications

FPC Conn. 2Pos Unsealed Cap Assy

Japanese

Application Specification

Japanese



Instruction Sheets

Instruction Sheet (non U.S.)

English

FPC Conn 2 Pos Unsealed Cap Assy

English