

FEATURES

- **Induction Heating Technology:** Provides efficient and uniform heating for safe bearing installation and removal
- **10 kg Maximum Bearing Weight:** Suitable for a wide range of bearing sizes and weights
- **Adjustable Inside Diameter:** Accommodates bearings with diameters from 20 mm to 160 mm, offering versatility
- **230 V Supply Voltage:** Compatible with standard industrial power supplies
- **Compliance with ANSI-ESD S20.20:2021 and RoHS:** Ensures adherence to safety and environmental standards

RS PRO Induction Bearing Heater, 10 kg Capacity

RS Stock No: 297-062



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

Product Description

The RS PRO Induction Bearing Heater is designed for efficient and uniform heating of bearings, facilitating easy installation and removal. With a maximum bearing weight capacity of 10 kg, it ensures precision and reliability in various industrial applications. Its induction heating technology provides rapid and controlled heating, reducing the risk of damage to the bearings.

General Specifications

Heater Type	Induction
Maximum Bearing Weight	10 kg
Maximum Inside Diameter	160 mm
Minimum Inside Diameter	20 mm
Product Type	Bearing Heater

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------

Electrical Specifications

Supply Voltage	230 V
----------------	-------



