



Main

Range of product	Odace
Product or component type	Data socket
Device presentation	Mechanism with fixing frame and central plate
Data socket type	RJ45 8 contact(s) Cat.6 <= 250 MHz
Type of packing	Paint cover

Complementary

Device mounting	Flush
Socket number	1
Organization of wire	Unshielded twisted pair
Cable shielding type	UTP
Product compatibility	Infraplus Actassi s-one
Fixing mode	By screws
Colour tint	Sustainable white (RAL 9003)
Surface finish	Dotted finish
Connections - terminals	IDC
Number of loop terminals	1
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: support frame
Height	71 mm
Width	71 mm
Depth	41.7 mm
Embedding depth	25.7 mm
Net weight	0.037 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
Standards	IEC 60603-7-5 ANSI/TIA/EIA-568-B-2-1 TIA/EIA-568 EN 50173-1 ISO/IEC 11801 IEC 60603-7 ANSI/TIA/EIA-568-B-2
IP degree of protection	IP21
IK degree of protection	IK04

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations