



Technical data

NJ221

Single row cylindrical roller bearings

Single row cylindrical roller bearing, single direction for axial loads, separable, pressed steel cage.

VISUAL (S)



PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	105 mm
D - External diameter	190 mm
B - Bearing/Inner ring width	36 mm
E - Upper roller diameter	168,8 mm
F - Under roller diameter	126,8 mm
d1 - IR flange outer diameter	135 mm
rs - Min fillet radius	2,1 mm
r1s - Min fillet radius	2,1 mm
Radial clearance class	CN
Mass	4,6 kg

PRODUCT PERFORMANCE	
C - Dynamic load	223000000 mN
C0 - Static load	241000000 mN
Cu - Fatigue limit load	26100000 mN
N lim - Oil lubrication limit speed	25800 °/s
N lim - Grease lubrication limit speed	21600 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT	
da min - Min shoulder diameter IR	116 mm
da max - Small face shoulder max diameter	124 mm
dc min - Min inner ring GO diameter	137 mm



ABUTMENT	
Da max - Max shoulder diameter OR	179 mm
ra max - Max fillet radius	2 mm

INDUSTRY CALCUL FACTORS	
Equivalent dynamic radial load	
$P = Fr$	
Equivalent static radial load	
$P_0 = Fr$	