


# mini slide

## DGSL-25-150-PA

Part number: 544037

FESTO

With position sensing, highly accurate, durable ball-cage guide, flexible damping on both sides without metallic end position (P).



### Data sheet

| Feature                                    | Value   |
|--|---|
| Stroke                                     | 150 mm  |
| Adjustable endposition range/front length  | 110 mm  |
| Adjustable endposition range/rear length   | 49 mm   |
| Piston diameter                            | 32 mm   |
| Operating mode of drive unit               | Yoke  |
| Cushioning                                 | P: Flexible cushioning rings/plates at both ends                            |
| Assembly position                          | Any   |
| Guide                                      | Ball bearing cage guide   |
| Design structure                           | Yoke<br>Piston<br>Piston rod<br>Slide                                       |
| Position detection                         | For proximity sensor  |
| Operating pressure                         | 1 ... 8 bar   |
| Max. speed                                 | 0.8 m/s   |
| Repetition accuracy                        | 0,3 mm  |
| Mode of operation                          | double-acting   |
| Operating medium                           | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                    |
| Note on operating and pilot medium         | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC    | 0 - No corrosion stress   |
| Ambient temperature                        | 0 ... 60 °C   |
| Impact energy in end positions             | 0.55 Nm   |
| Cushioning length                          | 1.3 mm  |
| Max. force F <sub>y</sub>                  | 4,800 N   |
| Max. force F <sub>z</sub>                  | 4,800 N   |
| Max. torque M <sub>x</sub>                 | 130 Nm  |
| Max. torque M <sub>y</sub>                 | 80 Nm   |
| Max. torque M <sub>z</sub>                 | 80 Nm   |
| Theoretical force at 6 bar, return stroke  | 415 N   |
| Theoretical force at 6 bar, advance stroke | 483 N   |
| Moving mass                                | 2,102 g   |
| Product weight                             | 5,556 g   |
| alternative connections                    | See product drawing   |
| Mounting type                              | with through hole   |
| Pneumatic connection                       | G1/8  |
| Materials note                             | Free of copper and PTFE<br>Conforms to RoHS                                 |
| Material cover                             | Wrought Aluminium alloy   |
| Material seals                             | HNBR  |
| Material housing                           | Wrought Aluminium alloy   |
| Material piston rod                        | High alloy steel, non-corrosive   |