



Data Sheet | Item Number: 294-4235

Lighting connector; push-button, external; with snap-in ground contact; DA+ DA- L PE N;
5-pole; Lighting side: for solid conductors; Inst. side: for all conductor types; max. 2.5
mm²; Surrounding air temperature: max 85°C (T85); white

<https://www.wago.com/294-4235>



Color: ■ white



Dimensions in mm

Field-wiring terminal block, 294 Series, with 10 mm pin spacing

Our field-wiring terminal block (item number 294-4235) is the ideal way to connect conductors quickly and easily. Ensure that the strip lengths are between 8 and 9 mm when connecting conductors to this field-wiring terminal block. This product features four conductor terminals and utilizes Push-in CAGE CLAMP® as well as PUSH WIRE®. Push-in CAGE CLAMP® technology provides a universal connection solution for any type of conductor. It allows both solid and fine-stranded conductors with ferrules to be inserted directly into the clamping point without the need for tools. Our proven PUSH WIRE® connection offers the fastest method for clamping conductors. It utilizes the conductor's stiffness to overcome the clamping spring's contact force. The dimensions are (50 x 17 x 27.3) mm (width x height x depth). Depending on the conductor type, this field-wiring terminal block is suitable for conductor cross sections ranging from 0.5 mm² to 2.5 mm² on one side and for conductor cross sections from 0.5 mm² to 2.5 mm² on the other side as well as conductor cross sections from 0.5 mm² to 1.5 mm² and from 0.5 mm² to 0.75 mm².

The contact surface is coated with tin.

Electrical data						
Ratings per		IEC/EN 60998-1			Ratings per IEC/EN – Notes	
Overvoltage category		III	III	II	Ratings (note)	Connection points
Pollution degree		3	2	2		
Nominal voltage		-	-	500 V		
Rated impulse withstand voltage		-	-	4 kV		
Rated current		-	-	24 A		

Ratings per		IEC/EN 60998-2-2			General information	
Overvoltage category		III	III	II	Wiring direction	Side-entry wiring
Pollution degree		3	2	2		
Nominal voltage		-	-	500 V		
Rated impulse withstand voltage		-	-	4 kV		
Rated current		-	-	24 A		



Connection Data

Clamping units	25
Total number of potentials	5
Number of connection types	4
PE function	Snap-in PE contact

Connection 1	
Connection type	External 1
Connection technology	Push-in CAGE CLAMP®
Number of connection points	2
Actuation type	Push-button
Connectable conductor materials	Copper
Solid conductor	0.5 ... 2.5 mm² / 18 ... 12 AWG
Solid conductor; push-in termination	0.5 ... 2.5 mm² / 18 ... 12 AWG
Stranded conductor	0.5 ... 2.5 mm² / 18 ... 14 AWG
Fine-stranded conductor	0.5 ... 2.5 mm² / 18 ... 14 AWG
Fine-stranded conductor; with insulated fer- rule	0.5 ... 1.5 mm² / 18 ... 16 AWG
Fine-stranded conductor; with uninsulated ferrule	0.5 ... 1.5 mm² / 18 ... 16 AWG
Fine-stranded conductor; with ferrule; push- in termination	0.5 mm² / 18 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches
Pole number	5
Wiring direction	Side-entry wiring

Connection 2	
Connection type	Internal 2
Connection technology	PUSH WIRE®
Number of connection points	1
Actuation type	Push-in
Solid conductor	0.5 ... 2.5 mm² / 18 ... 14 AWG
Fine-stranded conductor; with insulated fer- rule	0.5 ... 1 mm² / 18 ... 16 AWG
Fine-stranded conductor; with uninsulated ferrule	0.5 ... 1.5 mm² / 18 ... 14 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Connection 3	
Connection type	Internal 3
Connection technology	PUSH WIRE®
Number of connection points	1
Actuation type	Push-in
Solid conductor	0.5 ... 1.5 mm² / 18 ... 16 AWG
Fine-stranded conductor; with insulated fer- rule	0.5 ... 0.75 mm² / 18 AWG
Fine-stranded conductor; with uninsulated ferrule	0.5 ... 1 mm² / 18 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Connection 4	
Connection type	Internal 4
Connection technology	PUSH WIRE®
Number of connection points	1
Actuation type	Push-in
Solid conductor	0.5 ... 0.75 mm² / 18 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Physical data	
Pin spacing	10 mm / 0.394 inches
Width	50 mm / 1.969 inches
Height	17 mm / 0.669 inches
Depth	27.3 mm / 1.075 inches



Mechanical data		
Marking		DA+ DA- L ⊕ N
Mounting type		without snap-in mounting feet

Material data		
Note (material data)		Information on material specifications can be found here
Color		white
Material group		IIIa
Insulation material (main housing)		Polycarbonate (PC)
Flammability class per UL94		V0
Clamping spring material		Chrome-nickel spring steel (CrNi)
Contact material		Electrolytic copper (E _{Cu})
Contact Plating		Tin
Fire load		0.229 MJ
Halogen-free		Yes
Weight		16.1 g

Environmental requirements		
Temperature stability		120 °C
T marking		T85

Commercial data		
Product Group		8 (Misc. Chassis Mount Blocks)
PU (SPU)		250 pcs
Packaging type		Bag
Country of origin		PL
GTIN		4050821097907
Customs tariff number		85369010000

Product Classification		
UNSPSC		39121409
eCl@ss 10.0		27-14-11-06
eCl@ss 9.0		27-14-11-06
ETIM 9.0		EC001284
ETIM 10.0		EC001284
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption
SCIP notification number (Austria)		42bfa6b2-6913-4f72-be98-b97e0b920eea
SCIP notification number (Belgium)		78eff8cd-6d4c-4826-8846-c48e7a442307
SCIP notification number (Bulgaria)		7deed03f-8e0a-4358-bb83-6fd6cf581f17
SCIP notification number (Czech Republic)		b5d5c5f4-cf3b-4a35-9a7c-938bb53b1ae8
SCIP notification number (Denmark)		d13a98d9-b41a-41ed-980c-0167383ef2b8
SCIP notification number (Finland)		072ac21b-1a47-414d-9eca-5d96833a0180
SCIP notification number (France)		2ed04014-3f2c-4b26-943a-b21b0be82e18
SCIP notification number (Germany)		5f1ae9a5-8470-4ba4-92aa-4a3a89d94de1
SCIP notification number (Hungary)		fd76c449-e8c6-4f8a-8907-9d1913054fea
SCIP notification number (Italy)		f944028b-989b-417f-9bad-d58d5f9680e9
SCIP notification number (Netherlands)		2f09ab29-28ab-42b8-aaba-a32c73195e2f
SCIP notification number (Poland)		2bef43c7-d390-4168-9342-f3134ebc45c4
SCIP notification number (Romania)		1126fa3e-70df-4f08-8255-dc2d66eec525

Environmental Product Compliance	
SCIP notification number (Sweden)	32f1d023-0930-471a-ab61-7a7cad4a6112

Approvals / Certificates

General approvals		Declarations of conformity and manufacturer's declarations
		
Approval	Standard	Certificate Name
ENEC 05 DEKRA Certification B.V.	EN 60998	2128791.01
		EU-Declaration of Conformity WAGO GmbH & Co. KG
		UK-Declaration of Conformity WAGO GmbH & Co. KG

Downloads

Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 294-4235	

Documentation

Bid Text			
294-4235	19.02.2019	xml 5.59 KB	
294-4235	13.06.2017	doc 28.50 KB	

CAD/CAE-Data

CAD data	CAE data
2D/3D Models 294-4235 	WSCAD Universe 294-4235 
	ZUKEN Portal 294-4235 

1 Compatible Products

1.1 Optional Accessories

1.1.1 Strain relief

1.1.1.1 Strain relief

Item No.: 294-370
Strain relief; for 294 Series; with snap-in mounting feet; white

Item No.: 294-375
Strain relief; for 294 Series; without snap-in mounting feet; white

1.1.1.2 Strain relief plate

Item No.: 294-364
Strain relief plate; for 294 Series; for multi-core cables; 3- to 5-pole; with secured clamp; white

Item No.: 294-384
Strain relief plate; for 294 Series; for single strands; 3- to 5-pole; with secured clamp; white

1.1.2 Tool

1.1.2.2 Operating tool

Item No.: 206-294
Disconnection tool; green

Installation Notes

Installation

5-pole – with snap-in ground contact, d = 4.9 mm

Mounting hole for screw
Notice: The maximum thread diameter for self-tapping screws is 3 mm.

Hole for screw mount
Notice: The maximum thread diameter for self-tapping screws is 3 mm.

Conductor termination

Contact Technology

- Contact frame made of electrical copper, tin-plated
- Contacting spring made of high alloy (Cr-Ni spring steel)
- Contacting spring made of high alloy (Cr-Ni spring steel)

EUROPE
1 x 0.5 ... 2.5 mm ² "s"
1 x 0.5 ... 1.5 mm ² "s"
1 x 0.5 ... 0.75 mm ² "s"

AMERICA
1 x AWG 18 ... 14 "s"
1 x AWG 18 ... 16 "s"
1 x AWG 18 "s"

JAPAN
1 x 0.8 ... 1.6 mm diam. "s"
1 x 0.8 ... 1 mm diam. "s"
1 x 0.8 mm diam. "s"

EUROPE
2 x 0.5 ... 2.5 mm ² "s, str, f-str"

AMERICA
2 x AWG 18 ... 12 "s"
2 x AWG 18 ... 14 "s, f-str"


JAPAN
2 x 0.8 ... 2 mm diam. "s"
2 x 0.5 ... 2 mm ² str, f-str"

External connection
Internal connection

Internal connection:
PUSH WIRE® for internal wiring with solid conductors

External connection:
Push-in CAGE CLAMP® for field-wiring with all conductor types

Conductor termination



Terminating five conductors per pole – solid and fine-stranded.

