

Telephone Wipes #700-6409

RS Components

Chemwatch: 4882-11
Version No: 2.1.1.1
Material Safety Data Sheet according to NOHSC and ADG requirements

Chemwatch Hazard Alert Code: 2

Issue Date: 22/01/2014
Print Date: 22/01/2014
S.Local.AUS.EN

SECTION 1 IDENTIFICATION OF THE SUBSTANCE / MIXTURE AND OF THE COMPANY / UNDERTAKING

Product Identifier

Product name	Telephone Wipes #700-6409
Chemical Name	Not Applicable
Synonyms	Manufacturer's Code: 700-6409
Proper shipping name	Not Applicable
Chemical formula	Not Applicable
Other means of identification	Not Available
CAS number	Not Applicable

Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses	Office equipment cleaning product.
--------------------------	------------------------------------

Details of the supplier of the safety data sheet

Registered company name	RS Components	RS Components
Address	25 Pavasi Street Smithfield 2164 NSW Australia	Units 30 & 31, 761 Great South Road Penrose 1006 Auckland New Zealand
Telephone	+1 300 656 636	+64 9 526 1600
Fax	+1 300 656 696	+64 9 579 1700
Website	Not Available	www.rsnewzealand.com
Email	Not Available	Not Available

Emergency telephone number

Association / Organisation	Not Available	Not Available
Emergency telephone numbers	1800 039 008 (24 hours),+61 3 9573 3112	Not Available
Other emergency telephone numbers	1800 039 008 (24 hours),+61 3 9573 3112	Not Available

SECTION 2 HAZARDS IDENTIFICATION

Classification of the substance or mixture

HAZARDOUS SUBSTANCE. NON-DANGEROUS GOODS. According to the Criteria of NOHSC, and the ADG Code.

Label elements



Relevant risk statements are found in section 2

Poisons Schedule	
Risk Phrases ^[1]	R65 HARMFUL-May cause lung damage if swallowed.
Legend:	1. Classified by Chemwatch; 2. Classification drawn from HSIS ; 3. Classification drawn from EC Directive 1272/2008 - Annex VI
Indication(s) of danger	Xn

SAFETY ADVICE

S13	Keep away from food, drink and animal feeding stuffs.
S23	Do not breathe gas/fumes/vapour/spray.
S36	Wear suitable protective clothing.
S37	Wear suitable gloves.
S40	To clean the floor and all objects contaminated by this material, use water.
S46	If swallowed, seek medical advice immediately and show this container or label.

S56 Dispose of this material and its container at hazardous or special waste collection point.

Other hazards

Cumulative effects may result following exposure*.
May produce skin discomfort*.

SECTION 3 COMPOSITION / INFORMATION ON INGREDIENTS

Substances

See section below for composition of Mixtures

Mixtures

CAS No	%[weight]	Name
67-63-0	10-30	isopropanol
	NotSpec.	ingredients determined not to be hazardous

SECTION 4 FIRST AID MEASURES

Description of first aid measures

Eye Contact	<p>If this product comes in contact with the eyes:</p> <ul style="list-style-type: none"> ▶ Wash out immediately with fresh running water. ▶ Ensure complete irrigation of the eye by keeping eyelids apart and away from eye and moving the eyelids by occasionally lifting the upper and lower lids. ▶ Seek medical attention without delay; if pain persists or recurs seek medical attention. ▶ Removal of contact lenses after an eye injury should only be undertaken by skilled personnel.
Skin Contact	<p>If skin or hair contact occurs:</p> <ul style="list-style-type: none"> ▶ Flush skin and hair with running water (and soap if available). ▶ Seek medical attention in event of irritation.
Inhalation	<ul style="list-style-type: none"> ▶ If fumes, aerosols or combustion products are inhaled remove from contaminated area. ▶ Other measures are usually unnecessary.
Ingestion	<ul style="list-style-type: none"> ▶ Immediately give a glass of water. ▶ First aid is not generally required. If in doubt, contact a Poisons Information Centre or a doctor.

Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5 FIREFIGHTING MEASURES

Extinguishing media

	<ul style="list-style-type: none"> ▶ Water spray or fog. ▶ Alcohol stable foam. ▶ Dry chemical powder. ▶ BCF (where regulations permit). ▶ Carbon dioxide.
--	---

Special hazards arising from the substrate or mixture

Fire Incompatibility	Avoid contamination with strong oxidising agents as ignition may result
-----------------------------	---

Advice for firefighters

Fire Fighting	<ul style="list-style-type: none"> ▶ Alert Fire Brigade and tell them location and nature of hazard. ▶ Wear breathing apparatus plus protective gloves. ▶ Prevent, by any means available, spillage from entering drains or water courses. ▶ Use water delivered as a fine spray to control fire and cool adjacent area. ▶ DO NOT approach containers suspected to be hot.
Fire/Explosion Hazard	<p>Combustible Slight fire hazard when exposed to heat or flame Combustion products include:</p> <ul style="list-style-type: none"> • carbon monoxide (CO)

SECTION 6 ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Minor Spills	<ul style="list-style-type: none"> ▶ Remove all ignition sources. ▶ Clean up all spills immediately. ▶ Avoid breathing vapours and contact with skin and eyes. ▶ Control personal contact with the substance, by using protective equipment. ▶ Contain and absorb spill with sand, earth, inert material or vermiculite. ▶ Wipe up.
---------------------	---

Major Spills	<p>Minor hazard.</p> <ul style="list-style-type: none"> ▶ Clear area of personnel and move upwind. ▶ Alert Fire Brigade and tell them location and nature of hazard. ▶ Wear breathing apparatus plus protective gloves. ▶ Prevent, by any means available, spillage from entering drains or water course. ▶ No smoking, naked lights or ignition sources.
---------------------	--

Personal Protective Equipment advice is contained in Section 8 of the MSDS.

SECTION 7 HANDLING AND STORAGE

Precautions for safe handling

Safe handling	<p>Avoid generating and breathing vapour Avoid contact with eyes. Avoid prolonged and repeated skin contact. Avoid contact with incompatible materials.</p> <ul style="list-style-type: none"> ▶ No smoking, naked lights, heat or ignition sources. ▶ Wear personal protective equipment when handling
Other information	<p>Store away from sources of heat or ignition / naked lights. Store in a cool, dry and well-ventilated area.</p> <ul style="list-style-type: none"> ▶ Store away from incompatible materials. ▶ Keep containers securely sealed

Conditions for safe storage, including any incompatibilities

Suitable container	▶ Packaging as recommended by manufacturer.
Storage incompatibility	Avoid storage with oxidisers

PACKAGE MATERIAL INCOMPATIBILITIES

SECTION 8 EXPOSURE CONTROLS / PERSONAL PROTECTION

Control parameters

OCCUPATIONAL EXPOSURE LIMITS (OEL)

INGREDIENT DATA

Source	Ingredient	Material name	TWA	STEL	Peak	Notes
Australia Exposure Standards	isopropanol	Isopropyl alcohol	983 (mg/m ³) / 400 (ppm)	1230 (mg/m ³) / 500 (ppm)	Not Available	Not Available

EMERGENCY LIMITS

Ingredient	TEEL-0	TEEL-1	TEEL-2	TEEL-3
isopropanol	400(ppm)	400(ppm)	2000(ppm)	2000(ppm)

Ingredient	Original IDLH	Revised IDLH
isopropanol	12,000(ppm)	2,000 [LEL](ppm)

Exposure controls

Appropriate engineering controls	None under normal operating conditions.
Personal protection	
Eye and face protection	None under normal operating conditions.
Skin protection	See Hand protection below
Hand protection	None under normal operating conditions.
Body protection	See Other protection below
Other protection	None under normal operating conditions.
Thermal hazards	

Recommended material(s)

GLOVE SELECTION INDEX

Glove selection is based on a modified presentation of the:

"Forsberg Clothing Performance Index".

The effect(s) of the following substance(s) are taken into account in the **computer-generated** selection:

Telephone Wipes #700-6409

Material	CPI
----------	-----

Respiratory protection

Type A Filter of sufficient capacity. (AS/NZS 1716 & 1715, EN 143:2000 & 149:2001, ANSI Z88 or national equivalent)

Where the concentration of gas/particulates in the breathing zone, approaches or exceeds the "Exposure Standard" (or ES), respiratory protection is required.

Degree of protection varies with both face-piece and Class of filter; the nature of protection varies with Type of filter.

Telephone Wipes #700-6409

NEOPRENE	A
NITRILE	A
NITRILE+PVC	A
PE/EVAL/PE	A
PVC	B

* CPI - Chemwatch Performance Index

A: Best Selection

B: Satisfactory; may degrade after 4 hours continuous immersion

C: Poor to Dangerous Choice for other than short term immersion

NOTE: As a series of factors will influence the actual performance of the glove, a final selection must be based on detailed observation.

Required Minimum Protection Factor	Half-Face Respirator	Full-Face Respirator	Powered Air Respirator
up to 10 x ES	Air-line*	A-2	A-PAPR-2 ^
up to 20 x ES	-	A-3	-
20+ x ES	-	Air-line**	-

* - Continuous-flow; ** - Continuous-flow or positive pressure demand

^ - Full-face

A(All classes) = Organic vapours, B AUS or B1 = Acid gasses, B2 = Acid gas or hydrogen cyanide(HCN), B3 = Acid gas or hydrogen cyanide(HCN), E = Sulfur dioxide(SO₂), G = Agricultural chemicals, K = Ammonia(NH₃), Hg = Mercury, NO = Oxides of nitrogen, MB = Methyl bromide, AX = Low boiling point organic compounds(below 65 degC)

SECTION 9 PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Appearance	Colourless liquid impregnated cloth, card or tissue with a characteristic odour; soluble in water.		
Physical state	Liquid	Relative density (Water = 1)	Not Available
Odour	Not Available	Partition coefficient n-octanol / water	Not Available
Odour threshold	Not Available	Auto-ignition temperature (°C)	Not Available
pH (as supplied)	5-6	Decomposition temperature	Not Available
Melting point / freezing point (°C)	>0	Viscosity (cSt)	Not Available
Initial boiling point and boiling range (°C)	Not Available	Molecular weight (g/mol)	Not Applicable
Flash point (°C)	>55 (CC)	Taste	Not Available
Evaporation rate	Not Available	Explosive properties	Not Available
Flammability	Not Available	Oxidising properties	Not Available
Upper Explosive Limit (%)	Not Available	Surface Tension (dyn/cm or mN/m)	Not Available
Lower Explosive Limit (%)	Not Available	Volatile Component (%vol)	Not Available
Vapour pressure (kPa)	Not Available	Gas group	Not Available
Solubility in water (g/L)	Miscible	pH as a solution(1%)	Not Available
Vapour density (Air = 1)	Not Available	VOC g/L	

SECTION 10 STABILITY AND REACTIVITY

Reactivity	See section 7
Chemical stability	<ul style="list-style-type: none"> ▸ Presence of heat source and ignition source ▸ Presence of incompatible materials
Possibility of hazardous reactions	See section 7
Conditions to avoid	See section 7
Incompatible materials	See section 7
Hazardous decomposition products	See section 5

SECTION 11 TOXICOLOGICAL INFORMATION

Information on toxicological effects

Inhaled	The material is not thought to produce respiratory irritation (as classified by EC Directives using animal models). Nevertheless inhalation, of the material, especially for prolonged periods, may produce respiratory discomfort and occasionally, distress. Not considered to cause discomfort through normal use.
Ingestion	Considered an unlikely route of entry in commercial/industrial environments Ingestion may result in nausea, abdominal irritation, pain and vomiting
Skin Contact	The material is not thought to be a skin irritant (i.e. is unlikely to produce irritant dermatitis as described in EC Directives using animal models). Temporary discomfort, however, may result from prolonged dermal exposures. Good hygiene practice requires that exposure be kept to a minimum and that suitable gloves be used in an occupational setting. Not considered to cause discomfort through normal use.
Eye	Although the material is not thought to be an irritant (as classified by EC Directives), direct contact with the eye may produce transient discomfort characterised by tearing or conjunctival redness (as with windburn).

Telephone Wipes #700-6409

Chronic	Long-term exposure to the product is not thought to produce chronic effects adverse to health (as classified by EC Directives using animal models); nevertheless exposure by all routes should be minimised as a matter of course. Excessive use or prolonged contact may lead to defatting, drying and irritation of sensitive skin
----------------	---

Telephone Wipes #700-6409	TOXICITY	IRRITATION
	Not Available	Not Available

isopropanol	TOXICITY	IRRITATION
	Dermal (rabbit) LD50: 12800 mg/kg	Eye (rabbit): 10 mg - moderate
	Inhalation (Mouse) LC50: 53000 mg/m ³ /4h	Eye (rabbit): 100 mg - SEVERE
	Inhalation (Rat) LC50: 72600 mg/m ³ /4h	Eye (rabbit): 100mg/24hr-moderate
	Intraperitoneal (Guinea pig) LD50: 2560 mg/kg	Skin (rabbit): 500 mg - mild
	Intraperitoneal (Mouse) LD50: 4477 mg/kg	
	Intraperitoneal (Rabbit) LD50: 667 mg/kg	
	Intraperitoneal (Rat) LD50: 2735 mg/kg	
	Intravenous (Mouse) LD50: 1509 mg/kg	
	Intravenous (Rabbit) LD50: 1184 mg/kg	
	Intravenous (Rat) LD50: 1088 mg/kg	
	Oral (Mouse) LD50: 3600 mg/kg	
	Oral (Rabbit) LD50: 6410 mg/kg	
	Oral (Rat) LD50: 5000 mg/kg	
	Oral (rat) LD50: 5045 mg/kg	
Not Available	Not Available	

Not available. Refer to individual constituents.

ISOPROPANOL	For isopropanol (IPA): Acute toxicity: Isopropanol has a low order of acute toxicity. It is irritating to the eyes, but not to the skin. Very high vapor concentrations are irritating to the eyes, nose, and throat, and prolonged exposure may produce central nervous system depression and narcosis. Human volunteers reported that exposure to 400 ppm isopropanol vapors for 3 to 5 min.
--------------------	--

Acute Toxicity	Not Applicable	Carcinogenicity	Not Applicable
Skin Irritation/Corrosion	Not Applicable	Reproductivity	Not Applicable
Serious Eye Damage/Irritation	Not Applicable	STOT - Single Exposure	Not Applicable
Respiratory or Skin sensitisation	Not Applicable	STOT - Repeated Exposure	Not Applicable
Mutagenicity	Not Applicable	Aspiration Hazard	Aspiration Hazard Category 1

CMR STATUS

SECTION 12 ECOLOGICAL INFORMATION

Toxicity

Persistence and degradability

Ingredient	Persistence: Water/Soil	Persistence: Air
Not Available	Not Available	Not Available

Bioaccumulative potential

Ingredient	Bioaccumulation
Not Available	Not Available

Mobility in soil

Ingredient	Mobility
Not Available	Not Available

SECTION 13 DISPOSAL CONSIDERATIONS

Waste treatment methods

Product / Packaging disposal	Allow absorbed spillage to evaporate in an open top container, away from habitation. Bury or incinerate residue at an approved site.
-------------------------------------	---

SECTION 14 TRANSPORT INFORMATION**Labels Required**

Marine Pollutant	NO
HAZCHEM	Not Applicable

Land transport (ADG): NOT REGULATED FOR TRANSPORT OF DANGEROUS GOODS

Air transport (ICAO-IATA / DGR): NOT REGULATED FOR TRANSPORT OF DANGEROUS GOODS

Sea transport (IMDG-Code / GGVSee): NOT REGULATED FOR TRANSPORT OF DANGEROUS GOODS

Transport in bulk according to Annex II of MARPOL 73 / 78 and the IBC code

Source	Ingredient	Pollution Category	Residual Concentration - Outside Special Area (% w/w)	Residual Concentration
IMO MARPOL 73/78 (Annex II) - List of Other Liquid Substances	isopropanol	Not Available	Not Available	Not Available

SECTION 15 REGULATORY INFORMATION**Safety, health and environmental regulations / legislation specific for the substance or mixture**

<p>isopropanol(67-63-0) is found on the following regulatory lists</p>	<p>"Australia Exposure Standards", "IMO Provisional Categorization of Liquid Substances - List 2: Pollutant only mixtures containing at least 99% by weight of components already assessed by IMO", "IMO MARPOL 73/78 (Annex II) - List of Other Liquid Substances", "GESAMP/EHS Composite List - GESAMP Hazard Profiles", "IMO IBC Code Chapter 18: List of products to which the Code does not apply", "Australia Hazardous Substances Information System - Consolidated Lists", "International Agency for Research on Cancer (IARC) - Agents Reviewed by the IARC Monographs", "Sigma-Aldrich Transport Information", "Acros Transport Information", "Fisher Transport Information", "Australia Inventory of Chemical Substances (AICS)", "International Fragrance Association (IFRA) Survey: Transparency List", "IOFI Global Reference List of Chemically Defined Substances", "OECD List of High Production Volume (HPV) Chemicals", "Australia High Volume Industrial Chemical List (HVICL)", "Australia Dangerous Goods Code (ADG Code) - Dangerous Goods List", "Australia Dangerous Goods Code (ADG Code) - List of Emergency Action Codes", "International Maritime Dangerous Goods Requirements (IMDG Code)", "Belgium Federal Public Service Mobility and Transport, Regulations concerning the International Carriage of Dangerous Goods by Rail - Table A: Dangerous Goods List - RID 2013 (Dutch)", "International Air Transport Association (IATA) Dangerous Goods Regulations", "International Maritime Dangerous Goods Requirements (IMDG Code) - Substance Index", "Australia Quarantine and Inspection Service List of chemical compounds that are accepted solely for use at establishments registered to prepare meat and meat products for the purpose of the Export Control Act 1982", "Australia National Pollutant Inventory", "IMO IBC Code Chapter 17: Summary of minimum requirements", "OSPAR National List of Candidates for Substitution - Norway"</p>
---	---

SECTION 16 OTHER INFORMATION**Other information**

Classification of the preparation and its individual components has drawn on official and authoritative sources as well as independent review by the Chemwatch Classification committee using available literature references.

A list of reference resources used to assist the committee may be found at:

www.chemwatch.net/references

The (M)SDS is a Hazard Communication tool and should be used to assist in the Risk Assessment. Many factors determine whether the reported Hazards are Risks in the workplace or other settings. Risks may be determined by reference to Exposures Scenarios. Scale of use, frequency of use and current or available engineering controls must be considered.

This document is copyright. Apart from any fair dealing for the purposes of private study, research, review or criticism, as permitted under the Copyright Act, no part may be reproduced by any process without written permission from CHEMWATCH. TEL (+61 3) 9572 4700.