





ITEM #	PART #	REV	DESCRIPTION	QTY	Material	Weight
1	MDJ013	04	Nozzle body	1	Aluminium	5.66g
2	FPZ006	03	Compression spring	1	Music Wire	0.2g
3	HAZ002	03	5mm ball bearing	1	Chrome Steel	0.5g
4	MZZ011	05	Nozzle seat	1	Aluminium	0.7g




SECTION A-A



THIS DRAWING AND THE INFORMATION IT CONTAINS IS THE PROPERTY OF POWER ADHESIVES AND IS CONFIDENTIAL. IT MUST NOT BE REPRODUCED EITHER WHOLLY OR IN PART. ALL RIGHTS IN RESPECT OF PATENTS, DESIGNS AND COPYRIGHTS ARE RESERVED.

MATERIAL	N/A	DRAWN	SteveE
FINISH	N/A	DATE	22/02/2019
COLOUR	N/A	ECR No.	
NOTES			

DIMENSIONS ARE IN MM UNLESS OTHERWISE STATED THIRD ANGLE	TOLERANCES UNLESS OTHERWISE STATED WHOLE NUMBERS $\pm 0.5\text{mm}$ 1 DECIMAL PLACE $\pm 0.3\text{mm}$ 2 DECIMAL PLACE $\pm 0.1\text{mm}$	SCALE 1.5:1
	TITLE	SHEET 1 OF 2
DWG. No.	MPN - ADJ025	REVISION 01

	1	2	3	4	5	6								
A	General Table													
	Technical data													
	Type	Hot melt applicator nozzle												
	Material composition	Aluminium, steel, music wire												
	Weight	7g (0.25 oz)												
	Thread size	5/16 UNF												
	Nozzle hole size	2.5mm (0.1")												
	Sping rate	0.48 N/mm (2.75 lb/inch)												
B														
C														
D	 THIS DRAWING AND THE INFORMATION IT CONTAINS IS THE PROPERTY OF POWER ADHESIVES AND IS CONFIDENTIAL. IT MUST NOT BE REPRODUCED EITHER WHOLLY OR IN PART. ALL RIGHTS IN RESPECT OF PATENTS DESIGNS AND COPYRIGHTS ARE RESERVED.						MATERIAL	N/A	DRAWN	SteveE	DIMENSIONS ARE IN MM UNLESS OTHERWISE STATED  THIRD ANGLE	TOLERANCES UNLESS OTHERWISE STATED WHOLE NUMBERS ±0.5mm 1 DECIMAL PLACE ±0.3mm 2 DECIMAL PLACE ±0.1mm	SCALE 1.5:1	
							FINISH	N/A	DATE	22/02/2019			SHEET 2 OF 2	
							COLOUR	N/A	ECR No.		TITLE Standard nozzle			
							NOTES							
											DWG. No.		ADJ025	REVISION
											A4			01
								1	2	3	4	5	6	