



2 YEARS
MANUFACTURER
GUARANTEE

**500
+120
LUMEN**

**6/10h
MAX.**

USB RECHARGEABLE

360°

360°

Product number 1175670110
EAN 4007123691890

TECHNICAL DATA

Luminous flux	500 lm	Number of batteries	1
Total luminous flux secondary source	120 lm	Battery type	Built-in battery pack
Colour temperature	6500 K	Battery technology	Lithium-ion
Colour rendering index	80-89 (class 1B)	Impact strength	IK07
Battery capacity	2.5 Ah	Protection class	III
Battery voltage	3.7 V	Degree of protection (IP)	IP20
Light duration max.	10 h	Colour	black/grey
Battery charging time approx.	4 h		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.46 kg
Weight of product (without packaging)	0.28 kg	Dimension LxWxH (incl. packing)	5 cm x 12.5 cm x 34 cm
Dimension LxWxH (without packing)	4.2 cm x 6.2 cm x 27.3 cm		