


06400050

RCK 40 - Not self centering

2D Technical Drawing

Dynamic 3D View
Technical Specifications

Part number (CODE)	06400050
$\varnothing d$ (DD) mm	50
$\varnothing D$ (D) mm	80
L1 (L1) mm	20
L (L) mm	24
H (H) mm	34
Maximum torque Mt (MT) Nm	1770
Clamping pressure - Shaft (CPS) N/mm ²	190
Clamping pressure - Hub (CPH) N/mm ²	115
Clamping screws DIN 912 MAT. 12.9 - N. (CSN)	12
Clamping screws DIN 912 MAT. 12.9 - Type (CSTY)	M8x22
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTO) Nm	35
Extraction thread - Type (ETT)	M10
Extraction thread - N. (ETN)	4
Weight (WEIGHT) kg	0.60