

Rechargeable LED Hand Lamp HL 701 A, IP 54, 700+100 lm

Bright, handy and compact.



Product number 1175640010
EAN 4007123691241

DESCRIPTION

- 12 super-bright SMD LEDs at the front.
- Additional switching stage for 1 SMD LED in the luminaire head.
- Stepless dimming function 10 % to 100 % for particularly long light duration.
- Rubberised handle for optimum grip.
- Foldable holding foot up to +/- 90° with integrated magnet.
- 2 magnets at the back and fold-out hook for flexible use.
- Li-Ion battery 3.7 V/2.0 Ah with charge indicator
- USB C charging interface, including USB C charging cable

TECHNICAL DATA

| | | | |
|---|------------------|----------------------------------|-----------------------|
| Luminous flux | 700 lm | Number of batteries | 1 |
| Total luminous flux secondary source | 100 lm | Battery type | Built-in battery pack |
| Colour temperature | 5700 K | Battery technology | Lithium-ion |
| Colour rendering index | 80-89 (class 1B) | Impact strength | IK07 |
| Battery capacity | 2 Ah | Protection class | III |
| Battery voltage | 3.7 V | Degree of protection (IP) | IP54 |
| Light duration max. | 10 h | Colour | black |
| Battery charging time approx. | 3.5 h | | |

PACKAGING, DIMENSIONS AND WEIGHTS

| | | | |
|--|---------------------------|--|---------------------------|
| UP | 1 | Weight of product (including packaging) | 0.36 kg |
| Weight of product (without packaging) | 0.23 kg | Dimension LxWxH (incl. packing) | 8.7 cm x 6.2 cm x 27.8 cm |
| Dimension LxWxH (without packing) | 5.8 cm x 3.2 cm x 20.1 cm | | |

SCOPE OF DELIVERY

LED rechargeable hand lamp HL 701 A, 60cm USB C charging cable