

# ZCE64

limit switch head ZCE - side steel roller plunger  
horizontal



## Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product compatibility	XCMD XCKD XCKT XCKP
Associated body	ZCP39 ZCMD29C12 ZCMD37L1 ZCMD41L2 ZCMD25L5 ZCT26N12 ZCT21P16 ZCD29 ZCT21N12 ZCT28G11 ZCMD21L2 ZCMD39L5 ZCT26P16 ZCMD39L2 ZCMD37L2 ZCP27 ZCP21M12 ZCD31 ZCMD61C12 ZCD26 ZCD21M12 ZCT26G11 ZCMD29L2 ZCMD25L2 ZCMD21C12 ZCMD21M12 ZCP35 ZCMD21L1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCT28N12  
 ZCD35  
 ZCMD29L1  
 ZCD25  
 ZCMD81L2  
 ZCT27P16  
 ZCMD69C12  
 ZCD29M12  
 ZCMD25L1  
 ZCT27G11  
 ZCD37  
 ZCD21  
 ZCMD21L08U78  
 ZCT27N12  
 ZCP26  
 ZCMD81L5  
 ZCP29  
 ZCP29M12  
 ZCMD41L1  
 ZCT21G11  
 ZCP25  
 ZCMD41L5  
 ZCT25N12  
 ZCMD29L5  
 ZCMD39L1  
 ZCD28  
 ZCT25G11  
 ZCD27  
 ZCD39  
 ZCMD37L5  
 ZCT25P16  
 ZCP21  
 ZCP31  
 ZCMD81L1  
 ZCMD21L08R12  
 ZCMD61M12  
 ZCP28  
 ZCMD21L5  
 ZCP37  
 ZCT28P16

Movement of operating head	Linear
Type of operator	Side roller plunger spring return metal (with horizontal roller)
Type of approach	Lateral approach, 2 directions

### Complementary

Switch actuation	By 30° cam
Positive opening	Without

### Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------