

# Eaton 1713626

Catalog Number: 1713626

Eaton LPC Fixing rating plug 25A



General specifications

Product Name	Catalog Number
Eaton LPC Accessory Adapter plate	1713626
EAN	Product Length/Depth
8711426640009	140 mm
Product Height	Product Width
5 mm	100 mm
Product Weight	Compliances
0.002 kg	CE

## Product specifications

### Type

Adapter plate

### 10.10 Temperature rise

Not applicable.

### 10.11 Short-circuit rating

Not applicable.

### 10.12 Electromagnetic compatibility

Not applicable.

### 10.13 Mechanical function

Not applicable.

### 10.2.2 Corrosion resistance

Meets the product standard's requirements.

### 10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

### 10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

### 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

### 10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

### 10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

### 10.2.7 Inscriptions

Meets the product standard's requirements.

### 10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be

## Resources

### Catalogs

Product Range Catalog Industrial switch-disconnectors

[Eaton-industrial-switch-disconnectors-catalogue-ca008011en-en-gb.pdf](#)

### Declarations of conformity

[DA-DC-00004876.pdf](#)

[DA-DC-00004909.pdf](#)

### Installation instructions

[IL008052ZU](#)

evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### Frame

DII

#### Color

Yellow

#### Ambient operating temperature - max

50 °C

#### Ambient operating temperature - min

-25 °C

#### Equipment heat dissipation, current-dependent $P_{vid}$

0 W

#### Heat dissipation capacity $P_{diss}$

0 W

#### Heat dissipation per pole, current-dependent $P_{vid}$

0 W

#### Rated operational current ( $I_e$ ) - max

25 A

#### Rated operational current for specified heat dissipation ( $I_n$ )

0 A

#### Static heat dissipation, non-current-dependent $P_{vs}$

0 W



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)