

Medium Power Transistor (Motor, Relay drive) (60±10V, 2A)

2SD2143

Features


- 1) Built-in zener diode between collector and base.
- Strong protection against reverse surges due to "L" loads.
- 3) Built-in resistor between base and emitter.
- 4) Built-in damper diode.

● Absolute maximum ratings (Ta=25°C)

Parameter	Symbol	Limits	Unit	
Collector-base voltage	Vсво	60±10	V	
Collector-emitter voltage	VCEO	60±10	V	
Emitter-base voltage	VEBO	6	V	
Callantan aumant	la.	2	A (DC)	
Collector current	lc lc	3 *1	A (Pulse)	
Collector power dissipation	Pc	1	W	
Collector power dissipation	1	10	W (Tc=25°C)	
Junction temperature	Tj	150	°C	
Storage temperature	Tstg	-55 to +150	°C	

^{*1} Single pulse Pw=100ms


• Dimensions (Unit : mm)



● Packaging specifications and hfe

Туре	2SD2143
Package	CPT3
hfe	1k to 10k
Marking	_
Code	TL
Basic ordering unit (pieces)	2500

•Inner circuit



●Electrical characteristics (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions	
Collector-base breakdown voltage	ВУсво	50	-	70	V	Ic=50μA	
Collector-emitter breakdown voltage	BVceo	50	_	70	V	Ic=5mA	
Collector cutoff current	Ісво	-	-	1.0	μΑ	V _{CB} =40V	
Emitter cutoff current	Іево	_	_	3	mA	V _{EB} =5V	
Collector-emitter saturation voltage	V _{CE(sat)}	_	_	1.5	V	Ic/I _B =1A/1mA	*
DC current transfer ratio	hfe	1000	_	10000	_	Vce=2V, Ic=1A	
Transition frequency	f⊤	-	80	-	MHz	Vc=5V, I=-0.1A, f=30MHz	
Output capacitance	Cob	-	25	_	pF	Vcb=10V, Ie=0A, f=1MHz	

^{*} Measured using pulse current.

2SD2143 Data Sheet

•Electrical characteristics curves




Fig.1 Groundede emitter output characteristics (I)




Fig.2 Grounded emitter output characteristics (II)




Fig.3 Grounded emitter propagation characteristics




Fig.4 DC current gain vs. collector current (I)




Fig.5 DC current gain vs. collector current (II)




Fig.6 Collector-emitter saturation voltage vs. collector current




Fig.7 Collector-emitter saturation voltage vs. collector current




Fig.8 Collector output capacitance vs. collector-base voltage




Fig.9 Safe operating area (A. S. O) 2SD2143 (CPT)

Notes

No copying or reproduction of this document, in part or in whole, is permitted without the consent of ROHM Co.,Ltd.

The content specified herein is subject to change for improvement without notice.

The content specified herein is for the purpose of introducing ROHM's products (hereinafter "Products"). If you wish to use any such Product, please be sure to refer to the specifications, which can be obtained from ROHM upon request.

Examples of application circuits, circuit constants and any other information contained herein illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.

Great care was taken in ensuring the accuracy of the information specified in this document. However, should you incur any damage arising from any inaccuracy or misprint of such information, ROHM shall bear no responsibility for such damage.

The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM and other parties. ROHM shall bear no responsibility whatsoever for any dispute arising from the use of such technical information.

The Products specified in this document are intended to be used with general-use electronic equipment or devices (such as audio visual equipment, office-automation equipment, communication devices, electronic appliances and amusement devices).

The Products specified in this document are not designed to be radiation tolerant.

While ROHM always makes efforts to enhance the quality and reliability of its Products, a Product may fail or malfunction for a variety of reasons.

Please be sure to implement in your equipment using the Products safety measures to guard against the possibility of physical injury, fire or any other damage caused in the event of the failure of any Product, such as derating, redundancy, fire control and fail-safe designs. ROHM shall bear no responsibility whatsoever for your use of any Product outside of the prescribed scope or not in accordance with the instruction manual.

The Products are not designed or manufactured to be used with any equipment, device or system which requires an extremely high level of reliability the failure or malfunction of which may result in a direct threat to human life or create a risk of human injury (such as a medical instrument, transportation equipment, aerospace machinery, nuclear-reactor controller, fuel-controller or other safety device). ROHM shall bear no responsibility in any way for use of any of the Products for the above special purposes. If a Product is intended to be used for any such special purpose, please contact a ROHM sales representative before purchasing.

If you intend to export or ship overseas any Product or technology specified herein that may be controlled under the Foreign Exchange and the Foreign Trade Law, you will be required to obtain a license or permit under the Law.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/