


**FAG****6210-C-Z**

Deep groove ball bearing

Deep groove ball bearing 62...-C-Z, single row, Generation C, shield, steel sheet metal cage

Technical information



Your current product variant

Changed internal design	C	GenerationC
Sealing	Z	Non-contact shield on one Side
Cage	JN	Steel sheet metal
Tolerance class	P6	Class6 (P6), better than PN
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Without	Bearing not greased
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	50 mm	Bore diameter
D	90 mm	Outside diameter
B	20 mm	Width
C _r	40,000 N	Basic dynamic load rating, radial
C _{0r}	23,200 N	Basic static load rating, radial
C _{ur}	1,610 N	Fatigue load limit, radial
n _G	11,700 1/min	Limiting speed
n _{gr}	9,200 1/min	Reference speed
≈m	0.44 kg	Weight



Mounting dimensions

$d_{a\ min}$	57 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	83 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\ min}$	1.1 mm	Minimum chamfer dimension
D_1	78.64 mm	Shoulder diameter outer ring
D_2	81.65 mm	Caliber diameter outer ring
d_1	61.87 mm	Shoulder diameter inner ring
d_2	59.23 mm	Caliber diameter inner ring

Temperature range

$T_{\ min}$	-30 °C	Operating temperature min.
$T_{\ max}$	120 °C	Operating temperature max.

Calculation factors

f_0	14.4	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Sealed on one side