


Vishay High Power Products


Schottky Rectifier, 7.5 A



PRODUCT SUMMARY				
I _{F(AV)}	7.5 A			
V _R	35 to 45 V			
I _{RM} 15 mA at 125 °C				

FEATURES







RoHS*

- · High frequency operation
- · Low forward voltage drop
- Guard ring for enhanced ruggedness and long term reliability
- Lead (Pb)-free ("PbF" suffix)
- · Designed and qualified for industrial level

DESCRIPTION

The MBR7..PbF Schottky rectifier has been optimized for low reverse leakage at high temperature. The proprietary barrier technology allows for reliable operation up to 150 °C junction temperature. Typical applications are in switching power supplies, converters, freewheeling diodes, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS					
SYMBOL	CHARACTERISTICS	VALUES	UNITS		
I _{F(AV)}	Rectangular waveform	7.5	Α		
V_{RRM}		35 to 45	V		
I _{FSM}	$t_p = 5 \mu s sine$	690	Α		
V _F	7.5 Apk, T _J = 125 °C	0.57	V		
T _J	Range	- 65 to 150	°C		

VOLTAGE RATINGS				
PARAMETER	SYMBOL	MBR735PbF	MBR745PbF	UNITS
Maximum DC reverse voltage	V _R	35	45	V
Maximum working peak reverse voltage	V_{RWM}	33	45	V

ABSOLUTE MAXIMUM RATINGS					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum average forward current	I _{F(AV)}	T _C = 131 °C, rated V _R		7.5	Α
Non-repetitive peak surge current	I _{FSM}	5 μs sine or 3 μs rect. pulse	Following any rated load condition and with rated V _{RRM} applied	690	А
		Surge applied at rated load co- single phase 60 Hz	ndition half wave	150	
Non-repetitive avalanche energy	E _{AS}	$T_J = 25 ^{\circ}\text{C}, I_{AS} = 2 \text{A}, L = 3.5 \text{mH}$		7	mJ
Repetitive avalanche current	I _{AR}	Current decaying linearly to zero in 1 μ s Frequency limited by T _J maximum V _A = 1.5 x V _R typical		2	Α

^{*} Pb containing terminations are not RoHS compliant, exemptions may apply

MBR7..PbF Series

Vishay High Power Products Schottky Rectifier, 7.5 A



ELECTRICAL SPECIFICATIONS					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum forward voltage drop	V _{FM} ⁽¹⁾	15 A	T _J = 25 °C	0.84	
		7.5 A	T _J = 125 °C	0.57	V
		15 A		0.72	
Maximum instantaneous reverse current	I _{RM} ⁽¹⁾	T _J = 25 °C	Rated DC voltage	0.1	mA
		T _J = 125 °C		15	
Maximum junction capacitance	C _T	$V_R = 5 V_{DC}$ (test signal range 100 kHz to 1 MHz) 25 °C		400	pF
Typical series inductance	L _S	Measured from top of terminal to mounting plane		8.0	nΗ
Maximum voltage rate of change	dV/dt	Rated V _R 1000		1000	V/µs

Note

 $^{^{(1)}\,}$ Pulse width < 300 $\mu s,$ duty cycle < 2 %

THERMAL - MECHANICAL SPECIFICATIONS						
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES	UNITS	
Maximum junction temperate	ıre range	T_J		- 65 to 150	°C	
Maximum storage temperatu	ire range	T_{Stg}		- 65 to 175	- 0	
Maximum thermal resistance junction to case) ,	R_{thJC}	DC operation	3.0	°C/W	
Typical thermal resistance, case to heatsink		R _{thCS}	Mounting surface, smooth and greased	0.50	C/VV	
Approximate weight				2	g	
				0.07	OZ.	
Mounting torque —	minimum			6 (5)	kgf · cm	
	maximum			12 (10)	(lbf · in)	
Marking device			Case style TO-220AC	MBR745		



Schottky Rectifier, 7.5 A Vishay High Power Products




Fig. 1 - Maximum Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage (Per Leg)




Fig. 4 - Maximum Thermal Impedance ZthJC Characteristics (Per Leg)

Vishay High Power Products Schottky Rectifier, 7.5 A






Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current




Fig. 6 - Forward Power Loss Characteristics




Fig. 7 - Maximum Non-Repetitive Surge Current (Per Leg)

Note


 $\begin{array}{l} \mbox{(1)} \;\; \mbox{Formula used:} \; T_C = T_J - (Pd + Pd_{REV}) \; x \; R_{thJC}; \\ \mbox{Pd} = \mbox{Forward power loss} = I_{F(AV)} \; x \; V_{FM} \; \mbox{at} \; (I_{F(AV)}/D) \; (\mbox{see fig. 6}); \\ \mbox{Pd}_{REV} = \mbox{Inverse power loss} = V_{R1} \; x \; I_R \; (1 - D); \; I_R \; \mbox{at} \; V_{R1} = \mbox{Rated} \; V_R \\ \end{array}$



Schottky Rectifier, 7.5 A Vishay High Power Products

ORDERING INFORMATION TABLE

Device code



1 - Schottky MBR series

Current rating (7.5 A)

35 = 35 V

Voltage ratings -

45 = 45 V

None = Standard production

• PbF = Lead (Pb)-free

LINKS TO RELATED DOCUMENTS				
Dimensions http://www.vishay.com/doc?95221				
Part marking information http://www.vishay.com/doc?952				
SPICE model	http://www.vishay.com/doc?95298			

Document Number: 94299 Revision: 20-Aug-08





Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Revision: 11-Mar-11