

## Interface module - UM 25-18 MSTB/Front/Q - 2959502

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


VARIOFACE SLIM LINE, with screw connection and COMBICON header, for assembly at a right angle on NS 35/7.5, 18 positions



The illustration shows version UM 25-10 MSTB/Front/Q



### Key commercial data

Packing unit	1 pc
GTIN	 4 017918 086152
Weight per Piece (excluding packing)	123.12 g
Custom tariff number	85369010
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Width	25 mm
Height	217 mm
Depth	45 mm

#### Ambient conditions

Ambient temperature (operation)	-10 °C ... 50 °C
Ambient temperature (storage/transport)	-10 °C ... 70 °C

#### General

Max. permissible operating voltage	250 V AC/DC
Max. perm. current (per branch)	2.5 A
Number of positions	18
Mounting position	any
Degree of protection	IP00

# Interface module - UM 25-18 MSTB/FRONT/Q - 2959502

## Technical data

### General

Standards/regulations	IEC 60664
	DIN EN 50178
	IEC 62103
Rated insulation voltage	250 V
Rated surge voltage	2.2 kV (Functional insulation)
Pollution degree	2
Surge voltage category	II

### Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3

### Connection data for connection 2

Connection name	COMBICON connection
Number of connections	1
Connection method	COMBICON connectors
Number of positions	18

## Classifications

### eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

### ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604

# Interface module - UM 25-18 MSTB/FRONT/Q - 2959502

## Classifications

### ETIM

ETIM 5.0	EC002780
----------	----------

### UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

EAC
-----

## Accessories

### Necessary add-on products

Printed-circuit board connector - FRONT-MSTB 2,5/18-STF - 1779806

Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 18, Pitch: 5 mm, Connection method: Screw connection, Color: green, Contact surface: Tin



# Interface module - UM 25-18 MSTB/FRONT/Q - 2959502

## Accessories

Printed-circuit board connector - FKCT 2,5/18-STF - 1909566

Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 18, Pitch: 5 mm, Connection method: Spring-cage connection, Color: green, Contact surface: Tin



---

## Drawings

Circuit diagram

