
Features

- Excellent overall stability
- —Very tight tolerance down to ±0.05%
- —Extremely low TCR down to ±5 PPM/°C
- —High power rating up to 3 Watts
- —Excellent ohmic contact

RS PRO Metal Film Leaded Precision Resistor

RS Stock No.: MFR0623FADF4641, MFR0623FADF6801, MFR0623FADF1401




RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Applications

—Telecommunication
—Medical Equipment


Construction




①	Insulation Coating	⑤	Resistor Layer
②	Trimming Line	⑥	Marking
③	Ceramic Core	⑦	Lead Wire
④	Electrode Cap		

Type	L	D	H	d	Weight (g) (1000pcs)
RSPMFR0623	6.3±0.5	2.3±0.3	28±3.0	0.55±0.03	150

Derating Curve



Hot-Spot Temperature



RSPMFR1550

RSPMFR1145

MFR0932

RSPMFR0623(3/5W)

RSPMFR0623(1/4W / 1/2W)

RSPMFR0318(2/5W)

RSPMFR0318(1/8W / 1/4W)

Part Numbering

RSPMFR	0318	B	T	C	W	1001	
Product Type	Dimensions (L×D)	Resistance Tolerance	Packaging Code	TCR (PPM/˚C)	Power Rating	Resistance	Special
	0318: 3.3x1.8 0623: 6.3x2.3 0932: 9.0x3.2 1145: 11.5x4.5 1550: 15.5x5.0	A: ±0.05% B: ±0.1% C: ±0.25% D: ±0.5% F: ±1%	A: Ammo B: Bulk T: Taping Reel	S: ±5 B: ±10 N: ±15 C: ±25 D: ±50 E: ±100	R: 3W S: 2W T: 1W F: 3/5W U: 1/2W G: 2/5W V: 1/4W W: 1/8W	R100: 0.1Ω 0010: 1Ω 1000: 100Ω 2201: 2200Ω 1001: 1KΩ 1004: 1MΩ	: Standard MA: MA-type MC: MC-type FA: FA-type FB: FB-type FC: FC-type FD: FD-type

Standard Electrical Specifications

Item / Type	Power Rating at 70°C	Operating Temp. Range	Max. Operating Voltage	Max. Overload Voltage	Voltage Proof	Resistance Range ±0.05%	±0.1%	±0.25%	±0.5%	±1%	TCR (PPM/°C)
0318	1/8W	-55 ~ +155°C	150V	300V	300V	-	10Ω-1MΩ	10Ω-100KΩ		-	±5
						-	10Ω-1MΩ	10Ω-100KΩ		-	±10
						-	10Ω-1MΩ	-			±15
						-	10Ω-1MΩ				±25
							10Ω-1MΩ		10Ω-4.99MΩ	10Ω-10MΩ	±50
						-		10Ω-1MΩ	10Ω-4.99MΩ	0.1Ω-10MΩ	±100
0623	1/4W	-55 ~ +155°C	250V	500V	500V	10Ω-1MΩ				-	±5
						10Ω-1MΩ				100Ω-22KΩ	±10
						10Ω-1MΩ	10Ω-1MΩ	10Ω-499KΩ			±15
						10Ω-1MΩ	10Ω-1MΩ				±25
						-	10Ω-1MΩ		10Ω-4.99MΩ	10Ω-10MΩ	±50
						-	-	10Ω-1MΩ	10Ω-4.99MΩ	0.1Ω-10MΩ	±100
0932	1/2W	-55 ~ +155°C	350V	500V	500V	10Ω-1MΩ				-	±5
						10Ω-1MΩ				-	±10
						10Ω-1MΩ	10Ω-1MΩ	-			±15
						-	10Ω-1MΩ				±25
						-	10Ω-1MΩ		10Ω-4.99MΩ	10Ω-10MΩ	±50
						-		10Ω-1MΩ	10Ω-4.99MΩ	0.1Ω-10MΩ	±100
1145	1W	-55 ~ +155°C	500V	700V	700V	-	10Ω-1MΩ				±25
						-	10Ω-1MΩ		10Ω-4.99MΩ	10Ω-10MΩ	±50
						-		10Ω-1MΩ	10Ω-4.99MΩ	0.1Ω-10MΩ	±100
1550	2W	-55 ~ +155°C	500V	1000V	1000V	-	10Ω-1MΩ				±25
						-	10Ω-1MΩ		10Ω-4.99MΩ	10Ω-10MΩ	±50
						-		10Ω-1MΩ	10Ω-4.99MΩ	0.1Ω-10MΩ	±100

Operating Voltage=$\sqrt{}$(P*R) or Max. operating voltage listed above, whichever is lower.
Overload Voltage=2.5*$\sqrt{}$(P*R) or Max. overload voltage listed above, whichever is lower.
Value Range for standard resistance，below or over this resistance on request.

High Power & Ultra High Power Rating Electrical Specifications

Item / Type	Power Rating at 70°C	Operating Temp. Range	Max. Operating Voltage	Max. Overload Voltage	Voltage Proof	Resistance Range ±0.05%	±0.1%	±0.25%	±0.5%	±1%	TCR (PPM/°C)
0318	1/4W	-55 ~ +155°C	200V	400V	300V	-	10Ω-1MΩ				±25
						-	10Ω-1MΩ		10Ω-4.99MΩ	10Ω-10MΩ	±50
						-		10Ω-1MΩ	10Ω-4.99MΩ	0.1Ω-10MΩ	±100
	2/5W		200V	400V	300V	-	10Ω-1MΩ				±25
						-	10Ω-1MΩ		10Ω-4.99MΩ	10Ω-10MΩ	±50
						-		10Ω-1MΩ	10Ω-4.99MΩ	0.1Ω-10MΩ	±100
0623	1/2W	-55 ~ +155°C	300V	500V	500V	10Ω-1MΩ				-	±5
						10Ω-1MΩ				100Ω-22KΩ	±10
						10Ω-1MΩ		10Ω-499KΩ			±15
						10Ω-1MΩ					±25
						-	10Ω-1MΩ		10Ω-4.99MΩ	10Ω-10MΩ	±50
						-		10Ω-1MΩ	10Ω-4.99MΩ	0.1Ω-10MΩ	±100
	3/5W		350V	500V	500V	-	100Ω-22KΩ				±10
						-	10Ω-499KΩ				±15
						-	10Ω-1MΩ				±25
						-	10Ω-1MΩ		10Ω-4.99MΩ	10Ω-10MΩ	±50
						-		10Ω-1MΩ	10Ω-4.99MΩ	0.1Ω-10MΩ	±100
0932	1W	-55 ~ +155°C	400V	600V	500V	10Ω-1MΩ				-	±5
						10Ω-1MΩ				-	±10
						10Ω-1MΩ		-			±15
						10Ω-1MΩ					±25
						-	10Ω-1MΩ		10Ω-4.99MΩ	10Ω-10MΩ	±50
						-		10Ω-1MΩ	10Ω-4.99MΩ	0.1Ω-10MΩ	±100
1145	2W	-55 ~ +155°C	500V	700V	700V	-	10Ω-1MΩ				±25
						-	10Ω-1MΩ		10Ω-4.99MΩ	10Ω-10MΩ	±50
						-	10Ω-1MΩ		10Ω-4.99MΩ	0.1Ω-10MΩ	±100
1550	3W	-55 ~ +155°C	500V	1000V	1000V	-	10Ω-1MΩ				±25
						-	10Ω-1MΩ		10Ω-4.99MΩ	10Ω-10MΩ	±50
						-		10Ω-1MΩ	10Ω-4.99MΩ	0.1Ω-10MΩ	±100

Operating Voltage=$\sqrt{}$(P*R) or Max. operating voltage listed above, whichever is lower.
Overload Voltage=2.5*$\sqrt{}$(P*R) or Max. overload voltage listed above, whichever is lower.
Value Range for standard resistance，below or over this resistance on request.

Environmental Characteristics

Item	Requirement	Test Method
Resistance Value	1Ω-10MΩ	**IEC-60115-1 4.5** Measure at a distance of 10mm from the cap end
Short Time Overload	±(0.25%+0.05Ω)	**IEC-60115-1 4.13** 2.5 times RCWV for 5 seconds
Insulation Resistance	＞1000MΩ	**IEC-60115-1 4.6** The measure was executed by V-Block methods
Endurance	±(1.5%+0.05Ω)	**IEC-60115-1 4.25** 70±2°C, at RCWV (or Umax., whichever less) for 1000 hrs with 1.5 hrs “ON” and 0.5 hrs “OFF”
Damp Heat, Steady State	±(1.5%+0.05Ω)	**IEC-60115-1 4.24** 40±2°C, 90~95% R.H., for 56 days , loaded with 0.1 times RCWV (or Umax. whichever less)
Solderability	95% min. Coverage	**IEC-60115-1 4.17** 245±5°C for 3±0.5 seconds
Voltage Proof	By Type	**IEC-60115-1 4.7** In V-Block for 60 seconds
Temperature Coefficient	By Type	**IEC-60115-1 4.8** Resistance value at room temperature and room Temperature(+100°C)
Periodic-Pulse Overload Test	±(0.75%+0.05Ω)	**IEC-60115-1 4.39** 4 times RCWV(or Umax., whichever less) for 10000 cycles with 1sec “ON” and 25 sec “OFF”
Solvent Resistance of Marking	No obvious deterioration of coatings and markings	**IEC-60115-1 4.30** IPA for 5±0.5 min. with ultrasonic
Robustness of Terminations	Tensile: ≧ 2.5kg(24.5N)	**IEC-60115-1 4.16** Direct Load for 10 sec. In the direction off the terminal leads
Resistance to Soldering Heat	0318: ±(0.75%+0.05Ω) 0623&0932: ±(0.5%+0.05Ω) 1145&1550: ±(0.25%+0.05Ω)	**IEC-60115-1 4.18** The solder iron heated to 260°C±5°C and applied to the termination for a duration of 10±1 seconds
Temperature Cycling	±(0.75%+0.05Ω)	**IEC-60115-1 4.19** -55°C/125°C with 5 cycles. the duration at each temperature 30 min


RCWV(Rated continuous working voltage)= $\sqrt{}$(P*R) or Max. Operating voltage whichever is lower

■ **Storage Temperature: 25±10°C; Humidity < 80%RH**


Taping/Packing Specifications

1.Standard Type (Reel & Ammo)

Packing Methods




Reel Packing



（1） RESISTOR
（2） BANDOLIER
（3） PAPER
（4） FLANGE
（5） CYLINDER


Packaging / Type	Packing Methods			Reel Packing	
	A	B1-B2 Max	S	Across Flange (A)	Qty
0318	52+1/-0	1.2	5±0.3	72	5,000
	26+0.5/-0	1.0			
0623	52+1/-0	1.2	5±0.3	72	5,000
	26+0.5/-0	1.0			
0932	52+1/-0	1.2	5±0.3	72	2,500
1145	73+1/-0	1.5	5±0.3	95	2,000
	52+1/-0				
1550	73+1/-0	1.5	10±0.8	95	1,000
	52+1/-0				

Ammo Packing




Packaging / Type	Packing Methods			Ammo Packing			
	A	B1-B2 Max	S	A	B	C	Qty
0318	52+1/-0	1.2	5±0.3	79±2	73±3	257±5	5,000
	26+0.5/-0	1.0		52±2	74±3	252±5	
0623	52+1/-0	1.2	5±0.3	79±2	100±3	257±5	5,000
	26+0.5/-0	1.0		52±2	109±3	252±5	
0932	52+1/-0	1.2	5±0.3	79±2	58±3	257±5	1,000
1145	73+1/-0	1.5	5±0.3	103±2	82±3	262±5	1,000
	52+1/-0			81±2	85±3	256±5	
1550	73+1/-0	1.5	10±0.8	103±2	96±3	265±5	1,000
	52+1/-0			82±2	108±3	258±5	


2. Special Type (Bulk)




MA Type




MC Type




FA Type



FB Type




FC Type



FD Type

Codes	Type	P	H /H1/h	H2/G	J/ J1/J2	D	L	d	E
0318	MA	5±1	8.0±1	-	-	1.8±0.3	3.3±0.4	0.45±0.03	-
0623	MA	10±1	10.0±1	-	-	2.3±0.3	6.3±0.5	0.55±0.03	-
	FD	5~15	27.0±2	-	12±2	2.3±0.3	6.3±0.5	0.55±0.03	3±1
0932	MA	12.5±1	10.0±1	-	-	3.2±0.5	9.0±0.5	0.65±0.03	-
	MC	12.5±1	6.5±2	3.5±2	-	3.2±0.5	9.0±0.5	0.65±0.03	-
	FA	5~15	5.0±2	-	-	3.2±0.5	9.0±0.5	0.65±0.03	3±1
	FB	5~15	4.0±2	-	3±2	3.2±0.5	9.0±0.5	0.65±0.03	3±1
	FC	5~15	10.0±3	-	4±2	3.2±0.5	9.0±0.5	0.65±0.03	3±1
1145	MA	15±1	12.5±1	-	-	4.5±0.5	11.5±1.0	0.78±0.03	-
	MC	15±1	9.5±2	4.5±2	-	4.5±0.5	11.5±1.0	0.78±0.03	-
	FA	5~15	5.0±2	-	-	4.5±0.5	11.5±1.0	0.78±0.03	3±1
	FB	5~15	4.0±2	-	3±2	4.5±0.5	11.5±1.0	0.78±0.03	3±1
	FC	5~15	10.0±3	-	4±2	4.5±0.5	11.5±1.0	0.78±0.03	3±1
1550	MA	20±1	15.0±1	-	-	5.0±0.5	15.5±1.0	0.78±0.03	-
	MC	20±1	13.5±2	3.5±2	-	5.0±0.5	15.5±1.0	0.78±0.03	-
	FA	5~15	5.0±2	-	-	5.0±0.5	15.5±1.0	0.78±0.03	3±1
	FB	5~15	4.0±2	-	3±2	5.0±0.5	15.5±1.0	0.78±0.03	3±1
	FC	5~15	10.0±3	-	4±2	5.0±0.5	15.5±1.0	0.78±0.03	3±1

Marking & Resistance Tolerance



Cold	Digit	Multiplier	Tolerance	
Without	-	-	±20%	M
Silver	-	10^{-2}	±10%	K
Gold	-	10^{-1}	±5.0%	J
Black	0	10^{0}	-	-
Brown	1	10^{1}	±1.0%	F
Red	2	10^{2}	±2.0%	G
Orange	3	10^{3}	-	-
Yellow	4	10^{4}	-	-
Green	5	10^{5}	±0.50%	D
Blue	6	10^{6}	±0.25%	C
Violet	7	10^{7}	±0.10%	B
Grey	8	10^{8}	±0.05%	A
White	9	10^{9}	-	-

±1.00% ±0.50% ±0.25% ±0.10%	E-24	1.0	1.1	1.2	1.3	1.5	1.6	1.8	2.0	2.2	2.4	2.7	3.0	3.3	3.6	3.9	4.3	4.7	5.1	5.6	6.2	6.8	7.5	8.2	9.1
±1.00% ±0.50%	E-96	1.00	1.02	1.05	1.07	1.10	1.13	1.15	1.18	1.21	1.24	1.27	1.30	1.33	1.37	1.40	1.43	1.47	1.50	1.54	1.58	1.62	1.65	1.69	1.74
		1.78	1.82	1.87	1.91	1.96	2.00	2.05	2.10	2.15	2.21	2.26	2.32	2.37	2.43	2.49	2.55	2.61	2.67	2.74	2.80	2.87	2.94	3.01	3.09
		3.16	3.24	3.32	3.40	3.48	3.57	3.65	3.74	3.83	3.92	4.02	4.12	4.22	4.32	4.42	4.53	4.64	4.75	4.87	4.99	5.11	5.23	5.36	5.49
		5.62	5.76	5.90	6.04	6.19	6.34	6.49	6.65	6.81	6.98	7.15	7.32	7.50	7.68	7.87	8.06	8.25	8.45	8.66	8.87	9.09	9.31	9.53	9.76
±0.25% ±0.10%	E-192	10.0	10.1	10.2	10.4	10.5	10.6	10.7	10.9	11.0	11.1	11.3	11.4	11.5	11.7	11.8	12.0	12.1	12.3	12.4	12.6	12.7	12.9	13.0	13.2
		13.3	13.5	13.7	13.8	14.0	14.2	14.3	14.5	14.7	14.9	15.0	15.2	15.4	15.6	15.8	16.0	16.2	16.4	16.5	16.7	16.9	17.2	17.4	17.6
		17.8	18.0	18.2	18.4	18.7	18.9	19.1	19.3	19.6	19.8	20.0	20.3	20.5	20.8	21.0	21.3	21.5	21.8	22.1	22.3	22.6	22.9	23.2	23.4
		23.7	24.0	24.3	24.6	24.9	25.2	25.5	25.8	26.1	26.4	26.7	27.1	27.4	27.7	28.0	28.4	28.7	29.1	29.4	29.8	30.1	30.5	30.9	31.2
		31.6	32.0	32.4	32.8	33.2	33.6	34.0	34.4	34.8	35.2	35.7	36.1	36.5	37.0	37.4	37.9	38.3	38.8	39.2	39.7	40.2	40.7	41.2	41.7
		42.2	42.7	43.2	43.7	44.2	44.8	45.3	45.9	46.4	47.0	47.5	48.1	48.7	49.3	49.9	50.5	51.1	51.7	52.3	53.0	53.6	54.2	54.9	55.6
		56.2	56.9	57.6	58.3	59.0	59.7	60.4	61.2	61.9	62.6	63.4	64.2	64.9	65.7	66.5	67.3	68.1	69.0	69.8	70.6	71.5	72.3	73.2	74.1
		75.0	75.9	76.8	77.7	78.7	79.6	80.6	81.6	82.5	83.5	84.5	85.6	86.6	87.6	88.7	89.8	90.9	92.0	93.1	94.2	95.3	96.5	97.6	98.8