




1. FINISH: .00038[.000015] GOLD IN THE CONTACT AREA, .00254[.000100] MATTE TIN-LEAD ON REMAINDER OF CONTACT, ALL OVER .00127[.000050] NICKEL.
2. POINT OF MEASUREMENT FOR PLATING THICKNESS.
3. THE NOTED DIMENSIONS APPLY FROM THE BASIC DIMENSION CENTER LINE (NOT THE POST CENTER LINE) TO THE SURFACE INDICATED.
4. ONE POLARIZATION SLOT FOR 2 AND 3 POSITION ASSEMBLIES ONLY.
5. SELECT POST TAILS FORMED TO PROVIDE CONNECTOR HOLD DOWN UNTIL SOLDERED, CONFIGURATION ACCEPTS 0.69[.027]-2.03[.080] THICK PRINTED CIRCUIT BOARD. (SEE DETAIL Z).
6. PARTS ARE PACKAGED IN GANG OF TUBES.
7. DIMENSIONS NOTED ARE FOR SOLDER STENCIL LAYOUT FOR USE WITH 1.58±0.20[.062±.008] THICK PRINTED CIRCUIT BOARDS.
8. MATERIAL- HOUSING: HIGH TEMP THERMOPLASTIC, COLOR-BLACK.
POSTS: BRASS.
9. FINISH: .00038[.000015] GOLD IN THE CONTACT AREA, .00254[.000100] MATTE TIN ON REMAINDER OF CONTACT, ALL OVER .00127[.000050] NICKEL.

	33.02 [1.300]	30.99 [1.220]	1 1	12	6-104809-1
	30.48 [1.200]	28.45 [1.120]	10	1 1	6-104809-0
	27.94 [1.100]	25.91 [1.020]	9	10	5-104809-9
	25.40 [1.000]	23.37 [.920]	8	9	5-104809-8
	22.86 [.900]	20.83 [.820]	7	8	5-104809-7
	20.32 [.800]	18.29 [.720]	6	7	5-104809-6
	17.78 [.700]	15.75 [.620]	5	6	5-104809-5
	15.24 [.600]	13.21 [.520]	4	5	5-104809-4
	12.70 [.500]	10.67 [.420]	3	4	5-104809-3
	10.16 [.400]	8.13 [.320]	2	3	5-104809-2
	7.62 [.300]	5.59 [.220]	1	2	5-104809-1
	33.02 [1.300]	30.99 [1.220]	1 1	12	1-104809-1
	30.48 [1.200]	28.45 [1.120]	10	1 1	1-104809-0
	27.94 [1.100]	25.91 [1.020]	9	10	104809-9
	25.40 [1.000]	23.37 [.920]	8	9	104809-8
	22.86 [.900]	20.83 [.820]	7	8	104809-7
	20.32 [.800]	18.29 [.720]	6	7	104809-6
	17.78 [.700]	15.75 [.620]	5	6	104809-5
	15.24 [.600]	13.21 [.520]	4	5	104809-4
	12.70 [.500]	10.67 [.420]	3	4	104809-3
	10.16 [.400]	8.13 [.320]	2	3	104809-2
	7.62 [.300]	5.59 [.220]	1	2	104809-1
PLATING	C	B	A	NO. OF POSN	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: R BROWN 09FE01 CHK: K WRIGHT 09FE01		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.1% [.005] 3 PLC ± — 4 PLC ± — ANGLES ± —		NAME PLZD HDR ASSY, AMPMODU MTE, VERTICAL SINGLE ROW, 2.54[100] CL, 0.64[.025] SQ POSTS, WITH LATCHING & HOLD DOWN	
		APVD: K WRIGHT 09FE01 PRODUCT SPEC — APPLICATION SPEC —		SIZE CAGE CODE DRAWING NO RESTRICTED TO A1 00779 C 104809 —	
MATERIAL SEE NOTE 8		FINISH SEE TABLE		WEIGHT —	
CUSTOMER DRAWING				SCALE 4:1 SHEET 1 OF 1 REV 1.1	