

Titan tweezers 110 mm form 5


Art.-No.	5-031
Description	Titan tweezers 110 mm form 5
Application	Electronics, SMD/THT assembly, precision mechanics, watchmakers, jewelers, medical technology.
Specification	not serrated jaws

Material	Titan
Surface/Coating	matt finish
Features	antibacterial, antimagnetic, heat-resistant, solder-repellent:acid-resistant, non-reflecting, stainless, seawater resistant
Surface resistance	/

Shape	TG: Tapered tips straight
Icon No.	TG2

Dimensions and weight

A = 35 mm
B = 0.5 mm
C = 1 mm
Ai = /



length 110 mm
weight 9 g

Application and technical data

Tweezers are made entirely of TITAN (light metal) and meet the highest technical requirements. Melting point 1941 K (1668°C), thermal conductivity 22W, electrical conductivity 2.5×10^6 .