

## Power cable - SAC-3P-MSS/ 2,0-PVC PE SCO - 1411637

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Power cable, 3-position, PVC, black, Plug straight M12 SPEEDCON, S-coded, on free cable end, Cable length: 2 m, For AC current up to 16 A/230 V

### Why buy this product

- ✓ Easy and safe: 100% electrically tested plug-in components
- ✓ High-performance: AC connectors for up to 16 A and 230 V AC
- ✓ Protection against incorrect connection using special S-coding
- ✓ Save time, thanks to installation with SPEEDCON fast locking system



### Key commercial data

Packing unit	1 pc
GTIN	 4 046356 937375
Weight per Piece (excluding packing)	22.22 g
Custom tariff number	85444290
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length of cable	2 m
-----------------	-----

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 105 °C (Plug / socket)
Degree of protection	IP67

#### General

Rated current at 40°C	16 A
Rated voltage	230 V
Number of positions	3
Contact resistance	≤ 3 mΩ

## Power cable - SAC-3P-MSS/ 2,0-PVC PE SCO - 1411637

### Technical data

#### General

Insulation resistance	> 100 MΩ
Coding	S power
Status display	No
Protective circuit/component	Unwired
Surge voltage category	III
Pollution degree	3
Insertion/withdrawal cycles	> 100
Torque	0.4 Nm (M12 connector)

#### Material

Inflammability class according to UL 94	V0
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA
Material of grip body	TPU, hardly inflammable, self-extinguishing
Material, knurls	Zinc die-cast, nickel-plated

#### Cable

Cable type	PVC black
Cable type (abbreviation)	PVC
Cable abbreviation	LSYwYw-JZ
UL AWM style	2517 (105°C/300 V)
Conductor cross section	3x 1.5 mm <sup>2</sup>
AWG power supply	16
Conductor structure, voltage supply	30x 0.25 mm
Core diameter including insulation	2.4 mm ±0.1 mm
Wire colors	black 1, black 2, green/yellow
Overall twist	3 wires, twisted
External sheath, color	black
External cable diameter D	6.8 mm ±0.2 mm
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	12 x D
Cable weight	80 kg/km
Outer sheath, material	PVC
Material conductor insulation	PVC
Conductor material	Bare Cu litz wires
Insulation resistance	≥ 10 MΩ*km (at 20 °C)
Conductor resistance	≤ 13.3 Ω/km (at 20 °C)
Nominal voltage, cable	300 V AC
Test voltage, cable	2000 V AC
Flame resistance	According to IEC 60332-1
	According to DIN EN 60332-1-2

# Power cable - SAC-3P-MSS/ 2,0-PVC PE SCO - 1411637

## Technical data

### Cable

	According to VW-1
	According to FT1
Ambient temperature (operation)	-40 °C ... 90 °C (cable, fixed installation)
	-5 °C ... 90 °C (cable, flexible installation)

## Classifications

### eCl@ss

eCl@ss 5.1	27143423
eCl@ss 6.0	27061801
eCl@ss 8.0	27279218


### ETIM

ETIM 4.0	EC001855
ETIM 5.0	EC001855

## Drawings


### Schematic diagram

### Cable cross section



Pin assignment of M12 plug, 3-pos., PVC black [PVC] coded, view of pin side

### Dimensioned drawing



M12 x 1 plug, straight

