



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Tab**

Connector & Housing Type: **Cap**

Number of Positions: **3**

Terminal Orientation: **Straight**

Primary Product Color: **Natural**

Features

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Sealable	No
Connector System	Wire-to-Wire
Connector & Housing Type	Cap

Configuration Features

Number of Positions	3
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Terminal Type	Tab
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention Type	Latch



Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
Centerline (Pitch)	7.49 mm[.295 in]

Dimensions

Product Width	13.97 mm[.55 in]
Product Length	23.75 mm[.935 in]

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Also in the Series

Customers Also Bought

TE Part #2836077-1
[OCEAN_2.0_Applicator-S-070F100O-RSM](#)

TE Part #7-87522-2
[MOD IV RECP PLTD 30 DPLX LF](#)

TE Part #7-2266813-7
[OCEAN_2.0_SPARE_PART_KIT-055F062F](#)

TE Part #2151582-1
[OCEAN_2.0_Applicator-S-110F165O-RSM](#)

TE Part #7-2837932-7
[OCEAN_2.0_SPARE_PART_KIT-062F091O](#)

TE Part #7-2150373-7
[OCEAN-055F080F-CRIMPTOOLINGKIT](#)

TE Part #886281-000
[FLHTC0311-26-2](#)

TE Part #215882-6
[AMP-LATCH MIL TYPE RCPT CONNECTOR](#)

TE Part #926298-5
[UN-MNL STECK-GEH 4P](#)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_521274-2_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_521274-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_521274-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals



UL Report

English