

# DTM13-12PA-R005 ✓ ACTIVE

DEUTSCH | DEUTSCH DTM

TE Internal #: DTM13-12PA-R005

Right Angle, Wire-to-Board, 12 Position, 2 Rows, 4.19mm [.165in]

Centerline, Nickel (Ni), Sealable, Wire & Cable, DEUTSCH DTM

[View on TE.com >](#)



Automotive Parts > Automotive Connectors > Automotive Headers > DEUTSCH DTM Headers



PCB Mount Orientation: **Right Angle**

Contact Current Rating (Max): **7.5 A**

Termination Method to PCB: **Through Hole - Solder**

Sealable: **Yes**

Centerline (Pitch): **4.19 mm [.165 in]**

[All DEUTSCH DTM Headers \(38\)](#)

## Features

### Product Type Features

Connector Product Type	Connector Assembly
Mixed & Hybrid Header	No
Header Type	Fully Shrouded
Sealable	Yes
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Signal Positions	12
Number of Sections	1
PCB Mount Orientation	Right Angle
Number of Positions	12
Number of Rows	2

### Electrical Characteristics



Operating Voltage	250 VDC
Voltage Rating (Max)	250 VDC
Nominal Voltage Architecture	12 V, 24 V

### Body Features

Connector & Keying Code	A
Primary Product Color	Black

### Contact Features

Mating Pin Diameter	1.02 mm[.04 in]
Contact Type	Pin
Contact Current Rating (Max)	7.5 A
Contact Mating Area Plating Material	Nickel (Ni)

### Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

### Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Interface
PCB Mount Retention	With
Mounting Holes	With
PCB Mount Retention Type	Mounting Screw
Mating Alignment	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

### Housing Features

Centerline (Pitch)	4.19 mm[.165 in]
--------------------	------------------

### Dimensions

Connector Width	47.02 mm[1.851 in]
PCB Thickness (Recommended)	.78 – 2.36 mm[.031 – .093 in]
Profile Height from PCB	33.5 mm[1.319 in]
Connector Length	38.1 mm[1.5 in]

### Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]



### Operation/Application

Shielded	No
Circuit Application	Signal

### Industry Standards

IP Rating	Not Tested
UL Flammability Rating	UL 94V-0

### Packaging Features

Packaging Quantity	125
Packaging Method	Box

### Other

Interface Number	DTM04-12P
------------------	-----------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JAN 2025 (247)</p> <p>Candidate List Declared Against: JAN 2025 (247)</p> <p>SVHC &gt; Threshold:</p> <p>Dodecamethylcyclhexasiloxane (D6) (.5% in M-11264-1)</p> <p>Decamethylcyclopentasiloxane (D5) (.5% in M-11264-1)</p> <p>Pb (2.76% in 20855557814)</p> <p>Octamethylcyclotetrasiloxane (D4) (.5% in M-11264-1)</p> <p><b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these

limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | DEUTSCH DTM



## Customers Also Bought





TE Part #D369-P33-NS0  
369 3 WAY PLUG, NO CONTACTS,  
SKT



TE Part #D369-R66-NP1  
369 6 WAY REC, CRIMP, PIN



TE Part #3-1879355-1  
RR03 5% 75K AMMO



TE Part #1-5747150-3  
09 RCPT SP/FMS SCRLK



TE Part #2842126-4  
8P,2MM,BRK HDR,DRV,T,2.8,0.1AU,TB



TE Part #650074N006  
D-436-36CS454

## Documents

### Product Drawings

[HDR, 12P, BLK, RA, NI/CU, A](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_DTM13-12PA-R005\\_99\\_c-dtm13-12pa-r005-99.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_DTM13-12PA-R005\\_99\\_c-dtm13-12pa-r005-99.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_DTM13-12PA-R005\\_99\\_c-dtm13-12pa-r005-99.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

[Application Specification](#)

English

### Agency Approvals

[UL Report](#)

English