




Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: tris(2-methoxyethoxy)vinylsilane (.11% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 200277-4

BLOCK,50 POSN,M SERIES

Customers Also Bought



TE Part #1-1337430-0

BNC Str Plg Hex 50Ohm Silver Pltd RG174A



TE Part #5747150-2

09 RCPT SP/FMS STD




TE Part #201369-4

75 POS. PIN HOOD



TE Part #6-66461-2

SKT, .062 DIA, .025 SQ POST, LP



TE Part #6-87756-8

MOD IV RECP LP



TE Part #1-200835-1

SERIES "M" MIN. RECT. GUIDE SOC



TE Part #3-1393253-5

W68-X2Q12-25=M6/M7/M9/W6/W7



TE Part #5750071-1

Mini DIN, 6 pos, R/A, Shield



TE Part #102241-1

03 MODIV HSG COMP SR .100 POL



TE Part #8-6609107-0

PS0S0DS3B=C1264

Documents

Product Drawings

MALE BLOCK 50 PL.

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_201358-3_AK.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_201358-3_AK.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_201358-3_AK.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M_SERIES_PIN_AND_SOCKET_CONNECTORS](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[20 HVC, 34 AND 50 POSITION SERIES "M" CONNECTOR](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[LATCHING SHIELD AND PIN HOOD FOR 50 POSITION "M" SERIES CONNECTOR](#)

English

Agency Approvals

[Agency Approval Document](#)

English