

F36W T8 BL368 24

Item No: 0000092




SpeciaLITE®



The energy distribution of the BL368 lamp is concentrated around the spectral peak at 368nm which is the most important frequency for the attraction of flying insects.

Technical Assets

Dimensions (mm)



Photometrics

F36W T8 BL368 24

Item No: 0000092

SYLVANIA

General data

Product name	F36W T8 BL368 24
Technology	Fluorescent
Lamp shape	Tubular shape
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Enclosed
General application	SPG
Operating temperature range (°C)	-15°C...+40°C
ETIM Class	EC002962
E-number FI	4940425

Optical data

Ambient temperature for maximum luminous flux (°C)	25
Light colour	BL368 Blacklight
Adjustable chromaticity	N

Electrical data

Power consumption (W)	36
Wattage (W)	36.00
Supply current (A)	0.430
Primary Supply/Product voltage - min (V)	93
Primary Supply/Product voltage - max (V)	113
Control gear required	Yes
Dimmable	No
Dimming method	N/A
Drive current (mA)	430

Lifetime data

Average life (Nominal) (h)	9000
----------------------------	------

Physical data

Nominal Product Length (mm)	600.0
Nominal Product Diameter (mm)	26
Max. Length base to base (mm) - A	589.8
Length base to pin Min-Max (mm) - B	594.5-596.9
Max. Lamp Length (mm) - C/L	604.0
Max. Lamp Diameter (mm) - D	28.0
Weight (kg)	0.07

Packaging

Product EAN number	5410288000923
Packaging single length / height (cm)	61.0
Packaging single width (cm)	2.9
Packaging single depth (cm)	2.8
DUN14 (inner)	15410288000920
Units per outer package	25
Packaging outer length / height (cm)	63.0
Packaging outer width (cm)	15.5
Packaging outer depth (cm)	15.0

Safety data

Lamp mercury content (mg)	2.80
Optimal operating condition (°C)	-15-40
Breakage cleaning instructions	Applicable
Recommendation for disposal at end of life	Applicable
Special purpose lamp	Yes
Intended purpose	Flykilling - Insect attraction
Suitable for household illumination	No
Safety message	Not suitable for household